## **Vulite**°

# 4" TC REMODEL HOUSING

Project:
Fixture Type:
Location:
Contact/Phone:

INCANDESCENT LAMPS

VATCRW

#### PRODUCT DESCRIPTION

TC Remodel Housing designed for use in non-insulated areas • If installed where insulation is present, the insulation must be pulled back 3" from all sides of the TC housing • In Canada, when insulation is present, type IC fixture must be used • TC Remodel Housing for remodel application where back side of ceiling is not accessible • Installs through an opening in the ceiling from below • Secured in place by factory installed remodel springs.

## **PRODUCT SPECIFICATIONS**

Lamp Lamp ratings based on trim selected - see reverse.

**Socket** Floating medium base porcelain socket with nickel-plated copper screw shell • Shipped with socket cap to protect against paint overspray.

Trims Trim selection shown on reverse.

Labels UL/cUL listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps or insulation • UL/cUL Listed • Trim V4012 is wet location approved for covered ceiling applications • Trims V4017 and V4034 are wet location approved for covered ceiling applications, when used with outdoor rated lamps.

**Testing** All reports are based on published industry procedures; field performance may differ from laboratory performance.


Product specifications subject to change without notice.


### **INSTALLATION**

**Junction Box** Pre-wired junction box provided with removable access plate, (5) ½" knockouts and (4) Non-metallic sheathed cable connectors and ground wire • Knockouts equipped with pryout slots.

**Housing** TC housing, 22-gauge aluminum • Remodel springs accommodate up to a 5/8" ceiling thickness.

#### DIMENSIONS





4 3/8" CEILING CUTOUT

## ACCESSORIES

Catalog No.	Description
SMPLT-4	4" Housing Locator

To order, specify catalog number.

## **PRODUCT CODES**

Catalog Number	Input Voltage	Lamp Rating (max.)
V4TCRW	120V	PAR20/R20/PAR16/R16 (See reverse for mox. trim rating)



# 4" TC REMODEL HOUSING

INCANDESCENT LAMPS

## **V4TCRW**

## TRIMS/LAMPS

	Cat. No.	Description	Max. Lamp Rating
	V4034W-WH�� V4034B-WH��	White Baffle Black Baffle	50W PAR20, 50W R20
	V4017C-WH��	Clear Cone	50W PAR20, 50W R20
<b>3</b>	V4010-WH	White Ganbal Ring	SOW PAR2O
	V4018-WH	White Eyeball	60W PAR 16, 40W R 16
	V4012-WH*	Stippled Opal tens Shower with Reflector	50W PAR20, 50W R20

Trim Size: 5" O.D. Trim Finish: WH - White.

Note: In Canada when insulation is present, Type IC fixtures must be used.

- ♦ UL/cUL Listed for use in wet location.
- ♦♦ UL/cUL Listed for use in wet location with outdoor rated lamp.

