

Catalog Number	
Notes	Туре

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L3 and L3R.

CONSTRUCTION

Antiuge bronze, oil-rubbed bronze, brushed nickel and white finishes are one-piece aluminum reflectors with integral drop flange.

White reflector has polyester powder coat paint.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTINGS

U.L. Listed to U.S. and Canadian safety standards.

Wet location listed when used with Sylvania outdoor rated 75w PAR30 short neck safety lamp.

Reflector Patent # (U.S) 6116750.

Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.


NOTE: Specifications subject to change without notice.



3" Finishing Trim

3H20

WETLITENarrow Drop Flange



Specifications

Height: 3 (7.6)

Lamp Opening: 4 (10.2)

Diameter: 5-1/4 (13.3)


All dimensions are inches (centimeters) unless otherwise specified.

3" (7.6) 4" (10.2) — | — 5-1/4" (13.3) —

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Example: 3H20



	Housing Co	ompatibility	
Application	Source	Maximum wattage	Housing
IC/Non-IC	Incandescent	75 PAR30 Sylvania short neck	L3, L3R

Downlighting and Track Sheet #: 3H2O RLNS-170

3H2O 3" Wetlite Drop Flange Full Reflector Trim For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.