

FEATURES & SPECIFICATIONS

INTENDED USE

For entrances, stairwells, corridors, other pedestrian areas.

CONSTRUCTION

Cast aluminum backplate on which electrical components are mounted for maximum heat-dissipation. Gasketing between backplate and front cover prevents the entry of water and contaminants. External hardware includes phillips head and tamper-proof hex-head fasteners.

FINISH

Dark bronze (DDB) or white (DWH) front cover available for all wattages.

OPTICAL SYSTEM

Front cover/refractor is injection-molded, one-piece, UV-stabilized polycarbonate. Optical system is sealed and gasketed to inhibit entrance of outside contaminants.

ELECTRICAL SYSTEM

35W-70W HPS and 50W MH use 120V normal power factor.


Porcelain, medium-base socket with copper alloy nickel-plated screw shell and center contact. UL listed 660W, 600V, 4KV pulse rated. Medium-base lamp included with the fixture.

INSTALLATION

Units are for wall mounting and include two $3/4^{\rm *}$ knockouts for routing electrical conduit.

LISTING

UL listed for wet locations. Listed and labeled to comply with Canadian Standards.



Catalog Number

Notes


METAL HALIDE 50W HIGH PRESSURE SODIUM 35W, 50W, 70W 8' to 12' Mounting

Specifications

Height: 11" (27.9cm) Width: 6-1/2" (16.5cm) Depth: 5-1/4" (13.3cm) Weight: 4.9 lbs./2.2 kgs


ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**. Example: TWS 50M 120 PE LPI



Accessories

Order as separate catalog numbers RK1 PEB1 Photocell kit (120V only) TWSWG Wireguard Туре



Mounting Height Correction Factor

(Multiply the fc level by the correction factor) 10 ft. = .6412 ft. = .44



Sheet #: TWS-M-S ©2004-20

©2004-2010 Acuity Brands Lighting, Inc. All rights reserved. Rev. 3/1/10

Lithonia Lighting Outdoor Lighting One Lithonia Way, Conyers, GA 30012 Phone: 770-922-9000 Fax: 770-918-1209 www.lithonia.com