

## FEATURES & SPECIFICATIONS

**INTENDED USE** — The OLCFM provides years of maintenance-free general illumination for residential and commercial outdoor applications such as porches, covered walkways and store entrances.

**CONSTRUCTION** — Rugged cast-aluminum top-plate and outer-ring are protected by a thermoset powder coat finish that provides superior resistance to corrosion and weathering. A tightly controlled multi-stage process ensures a minimum 3 mils thickness for a finish that can withstand extreme climate changes without cracking or peeling.

Polycarbonate LED lens/cover protects LEDs.

Fixture weight = 2.98 lbs.

**OPTICS** — 96 high-performance LEDs produces up to 1077 lumens and maintain 70% of light output at 50,000 hours of service.

(LED lifespan based on IESNA LM-80-08 results and calculated per IESNA TM-21-11 methodology.)

White acrylic diffuser provides a soft white light at 4000K CCT

See Lighting Facts Labels for specific fixture performance.

**ELECTRICAL** — Fixture operates at 120 volts, 60 Hz.

Standard input = 16.6 watts

Operating temperature -30°C to 40°C.

Amps @ 120V = .131.

Surge protection = 2.5kV.

**INSTALLATION** — Mounts easily to existing junction box (by others).

**LISTINGS** — UL Listed to U.S. and Canadian safety standards for wet locations.

Designed for ceiling or wall mounting more than 4' above the ground.

Tested in accordance with IESNA LM-79 and LM-80 standards.

**WARRANTY** — 5-year limited warranty. Complete warranty terms located at [www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

Actual performance may differ as a result of end-user environment and application.



Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

Outdoor General Purpose

# OLCFM

OUTDOOR LED CAST FLUSH MOUNT



All dimensions are inches (centimeters) unless otherwise indicated.

### ORDERING INFORMATION

All configurations of this product are considered "standard" and have short lead times.

Example: OLCFM 15 DDB

OLCFM				
Series	Light Engine	Color Temperature (CCT) <sup>1</sup>	Voltage	Finish
OLCFM	15	(blank) 4000K	(blank) 120V	DDB Dark bronze WH White

### Notes

1 Nominal Correlated Color Temperature (CCT) per ANSI C78.377-2008.

# OLCFM Outdoor LED Cast Flush Mount

## PHOTOMETRIC DIAGRAMS

To see complete photometric reports or download .ies files for this product, visit [www.Lithonia.com](http://www.Lithonia.com). Tested in accordance with IESNA LM-79 and LM-80 standards.

