

## **FEATURES & SPECIFICATIONS**

**INTENDED USE** — LBL provides a digital lighting platform to deliver general ambient lighting for surface-mount applications. Light engine delivers long life and excellent color to ensure a sound quality, low-maintenance light installation.

**CONSTRUCTION** — Metal parts are die formed from code-gauge steel. Prismatic diffuser is 100% acrylic with sonically welded luminous ends. Continuous side flanges on fixture body provide light trap and continuous diffuser support to prevent accidental opening and simplify maintenance.

 $Finish:\ Five-stage\ iron\ phosphate\ pretreatment\ assures\ superior\ paint\ adhesion\ and\ rust\ resistance.$ 

Painted parts finished with high-gloss, high-reflectivity baked white polyester enamel (low VOC).

**OPTICS** — Curved prismatic diffuser with linear side prisms and highly transmissive overlay minimizes lamp image and provides high-angle brightness control. Luminous end plates soften appearance for improved aesthetics.

**ELECTRICAL** — Long-life LEDs, coupled with high-efficiency drivers, provide extended service life. LBL is rated to deliver L70 performance at 50,000 hours.

LISTINGS — CSA certified to U.S. and Canadian standards. Damp listed.

DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org/QPL to confirm which versions are qualified.

**WARRANTY** — 5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms and conditions.aspx

Note: Specifications subject to change without notice.

Catalog Number		
Notes		
Туре		

Contractor Select

# **LED Wraparound**

2' and 4' LED



Specifications

Length: 24 (61.0)

48 (122.0)

Width: 10 (25.4)

Depth: 2-3/4 (7.0)

2-3/4 (7.0)

All dimensions are inches (centimeters) unless otherwise indicated.

#### **MOUNTING DATA**


For unit or row installation, surface or stem mounting. Stem mounting not available on TLB units.

Individual Installation -

Two single-stem hangers required.

Row Installation -

One hanger per fixture plus one row required.



#### ORDERING INFORMATION

Catalog number	UPC	Description	Lumens	Color temperature	Lens type	Voltage	Wattage	Pallet qty	Standard carton qty.
LBL2 LP835	753573917564	2' LED Wraparound	2,000	3500K	Patterned #12 acrylic	120-277	26	112	1
LBL2 LP840	753573917595	2' LED Wraparound	2,000	4000K	Patterned #12 acrylic	120-277	26	112	1
LBL4 LP835	753573917601	4' LED Wraparound	4,000	3500K	Patterned #12 acrylic	120-277	50	56	1
LBL4 LP840	753573917632	4' LED Wraparound	4,000	4000K	Patterned #12 acrylic	120-277	50	56	1
LBL4 347 LP835	753573917649	4' LED Wraparound	4,000	3500K	Patterned #12 acrylic	347	50	56	1
LBL4 347 LP840	820476010279	4' LED Wraparound	4,000	4000K	Patterned #12 acrylic	347	50	56	1
LBL2 LP835 DIM	888791232363	2' LED Dimmable Wraparound	2,000	3500K	Patterned #12 acrylic	120-277	26	112	1
LBL2 LP840 DIM	888791232387	2' LED Dimmable Wraparound	2,000	4000K	Patterned #12 acrylic	120-277	26	112	1
LBL4 LP835 DIM	888791232417	4' LED Dimmable Wraparound	4,000	3500K	Patterned #12 acrylic	120-277	50	56	1
LBL4 LP840 DIM	888791232448	4' LED Dimmable Wraparound	4,000	4000K	Patterned #12 acrylic	120-277	50	56	1

#### Notes


- 347V option not available.
- Non-stock standard manufacturing lead times apply. Step-down transformer will not fit in LBL2.

CONTRACTOR SELECT / LED LED-WRAPAROUND

# LBL LED Wraparound

## **PHOTOMETRICS**

LBL2 LP835, 2010.5 delivered lumens, test no. LTL22712, tested in accordance to IESNA LM-79.



LBL4 LP835, 4050.9 delivered lumens, test no. LTL22675, tested in accordance to IESNA LM-79.

