

Gimbal Downlighting

Enhance your environment.

Adjustable Gimbal Downlighting in a range of sizes and bulb compatibility.

The Gimbal downlights are **adjustable and easy to install**—designed for Lithonia’s recessed 4”, 5”, and 6” housings in remodel and new construction applications. These fixtures provide **directional lighting for accent and sloped ceiling applications** and can be paired with **either a traditional or LED bulb**. They are available in 5 finishes—matte white, matte black, brushed nickel, oil-rubbed bronze, and clear diffuse.

- 4” Gimbal designed for use with LV3/LV3R low voltage or L3/L3R line voltage air tight recessed housings
- 5” and 6” Gimbals designed for use with L5/L5R and L7X/L7XR line voltage air tight recessed housings
- **Over 35 degree tilt in both directions** with 180 degree rotation to direct light where it is needed
- Easy Installation for new construction and remodel projects
- Ideal for accent, task, and slope ceiling recessed lighting needs



Learn more at www.lithonia.com

With a range of motion of over **35 degree tilt in both directions and a 180 degree horizontal rotation** this Gimbal family can be used in a variety of settings.



4G2 PAR/4G2 MR16

The 4" Gimbal is ideal for lower-height applications such as soffits, casework, and niches. This fixture is ideal for hospitality, retail, residential and apartment applications.



5G2 PAR

The 5" Gimbal is ideal for directing light to accent a display, wall hanging, sculpture, or to provide task lighting for a particular area. This fixture is ideal for hospitality, retail, residential and apartment applications.



6G2 PAR

The 6" Gimbal is ideal for slope ceilings, grazing textured surfaces, and highlighting artwork and other architectural features. This fixture is ideal for hospitality, retail, residential and apartment applications.

ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

Example: 4G2MW PAR20

Series	Finish	Lamps
4G2 4" Gimbal	MW Matte White	PAR20 50W PAR20 lamp MR16 50W MR16 lamp
	MB Matte Black	
	ORB Oil Rubbed Bronze	
	BN Brushed Nickel	
	A Clear Diffuse	

ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

Example: 5G2MW PAR30 TOR

Series	Finish	Lamps	Mounting Method
5G2 5" Gimbal	MW Matte White	PAR30 75W PAR30 lamp	TOR Torsion Springs
	MB Matte Black		
	ORB Oil Rubbed Bronze		
	BN Brushed Nickel		
	A Clear Diffuse		

ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

Example: 6G2MW PAR38 TOR

Series	Finish	Lamps	Mounting Method
6G2 6" Gimbal	MW Matte White	PAR38 75W PAR38 lamp	TOR Torsion Springs
	MB Matte Black		
	ORB Oil Rubbed Bronze		
	BN Brushed Nickel		
	A Clear Diffuse		



Please visit www.lithonia.com for more information.