











Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 <p>Eyeball with Baffle</p>	 <p>6 1/4"</p>		<p>208NW-WH - White Baffle, White Trim 208NB-WH - Black Baffle, White Trim</p>	<p>IC20/IC20W/IC20S/IC20R: 50W PAR20, 50W R20 IC20N/IC20NW: 50W PAR20, 50W R20 TC20/TC20S/TC20R: 50W PAR20, 50W R20 IC25/IC25W/IC25S/IC25R: 50W PAR20, 50W R20</p>
Adjustment: 35° Vertical, 358° rotation				
 <p>Gimbal Ring with Flat Trim</p>	 <p>6 1/4"</p>		<p>209N-WH - White Trim</p>	<p>IC20/IC20W/IC20S/IC20R: 75W PAR30 TC20/TC20S/TC20R: 75W PAR30 IC25/IC25W/IC25S/IC25R: 35W PAR30</p>
Adjustment: 30° Vertical, 358° rotation				
 <p>PAR30 Eyeball</p>	 <p>6 1/2"</p>		<p>529-ABZ - Classic Aged Bronze Trim 529-SC - Satin Chrome Trim 529-WH - White Trim</p>	<p>IC20/IC20W/IC20S/IC20R: 75W PAR30 IC20N/IC20NW: 50W PAR20, 50W R20 TC20/TC20S/TC20R: 75W PAR30 IC25/IC25W/IC25S/IC25R: 50W PAR30</p>
Adjustment: 30° Vertical, 358° rotation				
 <p>Gimbal Ring in Baffle</p>	 <p>6 1/4"</p>		<p>688W-WH - White Baffle, White Trim 688B-WH - Black Baffle, White Trim</p>	<p>IC20/IC20W/IC20S/IC20R: 50W PAR30 TC20/TC20S/TC20R: 75W PAR30 IC25/IC25W/IC25S/IC25R: 35W PAR30</p>
Adjustment: 30° Vertical, 358° rotation				
 <p>Gimbal Ring in Cone</p>	 <p>6 1/4"</p>		<p>689C-WH - Clear Alzak®, White Trim 689G-WH - Gold Alzak®, White Trim 689HZ-WH - Haze, White Trim 689WHZ-WH - Wheat Haze, White Trim 689WHZ-ABZ - Wheat Haze, Classic Aged Bronze Trim</p>	<p>IC20/IC20W/IC20S/IC20R: 50W PAR30 TC20/TC20S/TC20R: 75W PAR30 IC25/IC25W/IC25S/IC25R: 35W PAR30</p>
Adjustment: 30° Vertical, 358° rotation				