

MINIATURES



Pictures are not to scale. All lamps are clear.

Order code	Description	Lamp code	Shape	Base	Volts (V)	Amps (A)	Watts (W)	Average life (hrs)	Diameter (in.) (mm)	LCL (in.) (mm)	MOL (in.) (mm)	Pack qty
------------	-------------	-----------	-------	------	-----------	----------	-----------	--------------------	---------------------	----------------	----------------	----------

T (cont.)

50400	T5/CL/6V/1.5A/WDG/STD	908	T-5	Wedge	6.00	1.500	9	50	0.63 15.90	0.81 20.60	1.50 38.00	10
50402	T5/CL/12V/0.75A/WDG/STD	915	T-5	Wedge	12.00	0.750	9	50	0.63 15.90	0.81 20.60	1.50 38.00	10
22055	T5/CL/12.8V/0.31A/WDG/STD	901	T-5	Wedge	12.80	0.310	4	500	0.63 15.90	0.81 20.60	1.50 38.00	10
50403	T5/CL/12.8V/0.56A/WDG/STD	918	T-5	Wedge	12.80	0.560	7	50	0.63 15.90	0.81 20.60	1.50 38.00	10
50401	T5/CL/12.8V/1A/WDG/STD	912	T-5	Wedge	12.80	1.000	13	1200	0.63 15.90	0.81 20.60	1.50 38.00	10
50404	T5/CL/12.8V/1.4A/WDG/STD	921	T-5	Wedge	12.80	1.400	18	500	0.63 15.90	0.81 20.60	1.50 38.00	10
50399	T5/CL/13V/0.69A/WDG/STD	906	T-5	Wedge	13.00	0.690	9	1000	0.63 15.90	0.81 20.60	1.50 38.00	10
50398	T5/CL/13.5V/0.69A/WDG/STD	904	T-5	Wedge	13.50	0.690	9	5000	0.63 15.90	0.81 20.60	1.50 38.00	10
50318	9T5/CL/24V/WDG/STD	EMS-2409W	T-5	Wedge	24.00	0.375	9	75	0.63 15.90	0.81 20.60	1.50 38.00	10
50320	18T5/CL/24V/WDG/STD	EMS-2218W	T-5	Wedge	24.00	0.750	18	75	0.63 15.90	0.81 20.60	1.50 38.00	10
13022	10T5.5/CL/130V/E14	N/A	T-5.5	E14	130.00	0.077	10	2000	0.74 18.80	1.48 37.50	2.13 54.00	10
50705	T5.5K/CL/30V/0.04A/SLB/STD	ATS-5804	T-5.5K	Slide Base 5.4x4.8 mm	30.00	0.040	1	5000	0.22 5.50	0.79 20.00	0.87 22.00	10
50708	5T6/CL/24V/BA15d/STD	SP-117	T-6	BA15d	24.00	0.208	5	1000	0.75 19.10	1.13 28.60	1.89 48.00	10
50709	10T6/CL/115V/BA15d/STD	SP-22	T-6	BA15d	115.00	0.087	10	1000	0.75 19.10	1.13 28.60	1.89 48.00	10
50259	1.2T6.8/CL/60V/BA7s/STD	6020S	T-6.8	BA7s	60.00	0.012	1	5000	0.27 6.80	0.75 18.98	0.79 20.00	10
22022	25T8/CL/12V/BAY15d/STD	1230U	T-8	BAY15d	12.00	2.083	25	1000	1.00 25.40	1.38 35.00	2.72 69.00	10
22025	25T8/CL/24V/BAY15d/STD	2430U	T-8	BAY15d	24.00	1.042	25	1000	1.00 25.40	1.38 35.00	2.72 69.00	50
22026	25T8/CL/32V/BAY15d/STD	3225U	T-8	BAY15d	32.00	0.781	25	1000	1.00 25.40	1.38 35.00	2.72 69.00	10
50713	15T8/CL/130V/E14/STD	SP-59U	T-8	E14	130.00	0.115	15	2000	1.00 25.40	1.73 43.90	2.56 65.00	10
50714	25T8/CL/130V/E14/STD	SP-60U	T-8	E14	130.00	0.192	25	2000	1.00 25.40	1.73 43.90	2.56 65.00	10
22070	15T8/CL/240V/E14/STD	SP-61U	T-8	E14	240.00	0.063	15	2000	1.00 25.40	1.73 43.90	2.56 65.00	10
10378	25T8/CL/240V/E14/STD	SP-70U	T-8	E14	240.00	0.104	25	2000	1.00 25.40	1.73 43.90	2.56 65.00	10
58706	T10/CL/110V/BA9s/STD	N/A	T-10	BA9s	110.00	0.080	9	10000	0.39 10.00	0.97 24.53	1.11 28.30	10
22050	5T11/CL/12V/S8.5d/STD	A6413	T-11	S8.5d	12.00	0.417	5	4100	0.39 10.00	0.79 20.00	1.57 40.00	10
50315	5T11/CL/24V/S8.5d/STD	A6424	T-11	S8.5d	24.00	0.208	5	1000	0.39 10.00	0.87 22.00	1.73 44.00	10
50314	5T11/CL/24V/S8.5d/STD	A6423	T-11	S8.5d	24.00	0.208	5	1000	0.39 10.00	0.79 20.00	1.54 39.00	10
22057	10T11/CL/24V/S8.5d/STD	A6425	T-11	S8.5d	24.00	0.417	10	1000	0.39 10.00	0.87 22.00	1.73 44.00	10
22122	40T12/CL/24V/P28s/STD	2450C	T-12	P28s	24.00	1.667	40	1000	1.50 38.10	1.77 45.00	2.72 69.00	25
22118	60T12/CL/110V/P28s/STD	1150C	T-12	P28s	110.00	0.545	60	1000	1.50 38.00	1.77 45.00	4.07 103.50	10
50712	5T17mm/CL/24V/E14/STD	SP-56U	T-17	E14	24.00	0.208	5	2000	0.67 17.00	1.38 35.00	2.13 54.00	10
22068	5T17mm/CL/130V/E14/STD	SP-54U	T-17	E14	130.00	0.038	5	2000	0.67 17.00	1.38 35.00	2.13 54.00	10

This list only shows a portion of the whole selection of miniature lamps available at STANDARD's. For a complete product listing visit our e-catalog at www.standardpro.com.