


Features

- Uses 80 % less energy than incandescent lamps
- Lasts 10 times longer than incandescent lamps
- Available in a wide range of colour temperatures
- Slimmer designer
- Starting temperature: -18 °C/0 °F
-  Visit our website for a complete listing of all E-LUME ENERGY STAR qualified products

-  us listed

Benefits

- Suitable for use in totally enclosed fixtures
- Fits most fixtures
- Long Life
- Saves on energy and maintenance costs



Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Incandescent equivalent (W)	Case qty
62764	CF7/T2/27K/SPIRAL/E26/ELUME	7	E26	2 700	82	10 000	430	40	48
61020	CF9/T2/27K/SPIRAL/E26/ELUME	9	E26	2 700	82	10 000	550	40	48
62311	CF9/T2/41K/SPIRAL/E26/ELUME	9	E26	2 700	82	10 000	550	40	48
62765	CF11/T2/27K/SPIRAL/E26/ELUME	11	E26	2 700	82	10 000	730	40	48
61021	CF13/T2/27K/SPIRAL/E26/ELUME	13	E26	2 700	82	10 000	900	60	48
61024	CF13/T2/30K/SPIRAL/E26/ELUME	13	E26	2 700	82	10 000	900	60	48
61026	CF13/T2/35K/SPIRAL/E26/ELUME	13	E26	3 500	82	10 000	850	60	48
61029	CF15/T2/27K/SPIRAL/E26/ELUME	15	E26	2 700	82	10 000	1 010	60	48
61030	CF15/T2/30K/SPIRAL/E26/ELUME	15	E26	3 000	82	10 000	1 010	60	48
61031	CF20/T2/27K/SPIRAL/E26/ELUME	20	E26	2 700	82	10 000	1 330	75	48
61032	CF23/T2/27K/SPIRAL/E26/ELUME	23	E26	2 700	82	10 000	1 600	100	48
61033	CF23/T2/30K/SPIRAL/E26/ELUME	23	E26	3 000	82	10 000	1 600	100	48
61034	CF23/T2/41K/SPIRAL/E26/ELUME	23	E26	4 100	82	10 000	1 600	100	48
61035	CF23/T2/50K/SPIRAL/E26/ELUME	23	E26	5 000	82	10 000	1 600	100	48

12 pack



4 pack



Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Incandescent equivalent (W)	Case qty
61022	CF13/T2/27K/SPIRAL/E26/ELUME 4P	13	E26	2 700	82	10 000	900	60	64
61025	CF13/T2/30K/SPIRAL/E26/ELUME 4P	13	E26	3 000	82	10 000	900	60	64
61027	CF13/T2/41K/SPIRAL/E26/ELUME 4P	13	E26	4 100	82	10 000	880	60	64
61028	CF13/T2/50K/SPIRAL/E26/ELUME 4P	13	E26	5 000	82	10 000	880	60	64
61023	CF13/T2/27K/SPIRAL/E26/ELUME 12P	13	E26	2 700	82	10 000	900	60	48