



T8

IS=Instant Start PS=Program Start

No. of lamps	Primary lamp type	Input volts (V)	Starting method	Order code	Description	Max. case temp. (°C)	Input power ANSI (W)	Ballast factor	Input current (A)	Lamps operated				F17T8 F25T8
										F32T8	F30T8ES	F28T8ES	F25T8ES	
1	F32T8	120	IS	31010	E132T8IS120/N	75	28	0.90	0.23	✓	✓	✓	✓	✓
			IS	31037	E132T8IS120/L	75	25	0.78	0.21	✓	✓	✓	✓	✓
			IS	56556	E132T8IS120/L/BULK	75	25	0.78	0.21	✓	✓	✓	✓	✓
		347	IS	56557	E132T8IS347/L/BULK	75	25	0.78	0.07	✓	✓	✓	✓	✓

No. of lamps	Primary lamp type	Input volts (V)	Starting method	Order code	Description	Max. case temp. (°C)	Input power ANSI (W)	Ballast factor	Input current (A)	Lamps operated				F17T8 F25T8 F40T8
										F32T8	F30T8ES	F28T8ES	F25T8ES	
2	F32T8	120	IS	61113	E232T8IS120/N/AS	75	55	0.87	0.49	✓	✓	✓	✓	✓
			IS	61124	E232T8IS120/N/AS/BULK	75	55	0.87	0.49	✓	✓	✓	✓	✓
			IS	56558	E232T8IS120/L/BULK	75	48	0.77	0.39	✓	✓	✓	✓	✓
			IS	61123	E232T8IS120/L/AS	75	48	0.77	0.45	✓	✓	✓	✓	✓
			IS	61126	E232T8IS120/L/AS/BULK	75	48	0.77	0.45	✓	✓	✓	✓	✓
			IS	60075	E232T8IS120/H/90C	90	74	1.20	0.64	✓	✓	✓	✓	✓
		120-277	IS	61128	E232T8IS120-277/N/AS	75	55	0.89	0.46	✓	✓	✓	✓	✓
			IS	61130	E232T8IS120-277/N/AS/BULK	75	55	0.89	0.46	✓	✓	✓	✓	✓
			IS	61131	E232T8IS120-277/L/AS	75	48	0.77	0.40	✓	✓	✓	✓	✓
			IS	61132	E232T8IS120-277/L/AS/BULK	75	48	0.77	0.40	✓	✓	✓	✓	✓
			PS	61061	E232T8PS120-277/N/AS/BULK	90	57	0.88	0.48	✓	✓	✓	✓	✓
			PS	61062	E232T8PS120-277/L/AS/BULK	90	52	0.78	0.43	✓	✓	✓	✓	✓
		347	PS	57031	E232T8PS120-277/H/XTRM	90	75	1.20	0.62	✓	✓	✓	✓	✓
			IS	10293	E232T8IS347/N	75	55	0.87	0.16	✓	✓	✓	✓	✓
			IS	31549	E232T8IS347/N/BULK	75	55	0.87	0.16	✓	✓	✓	✓	✓
			IS	58278	E232T8IS347/L/BULK	75	50	0.76	0.14	✓	✓	✓	✓	✓
			IS	60076	E232T8IS347/H/90C	90	74	1.20	0.21	✓	✓	✓	✓	✓
			PS	62992	E232T8PS347/N/AS/BULK	75	56	0.88	0.16	✓	✓	✓	✓	✓



Electronic Fluorescent Ballasts