

Features

- Soft pleasant light
- Fit most type of lamps
- Excellent lumen maintenance
- Excellent CRI (97)
- Decorative
- Dimmable
- Instant on

Applications

- Residential
- Restaurants
- Marquees
- Track lighting
- Office buildings
- Architectural signage
- Hotels
- Retail stores
- Decorative lighting



Order code	Description	Watts (W)	Base	Volts (V)	Finish	Filament	Average life (hrs)	Initial lumens (lm)	LCL (in. / mm)		Case qty
A19											
1 52448	40A19/F/6M/130V/ELUME 6P	40	E26	130	Frost	C-9	6000	285	3 1/8	79	120
1 52451	60A19/F/1M/120V/ELUME 6P	60	E26	120	Frost	C-9	1000	820	3 1/8	79	120
1 52449	60A19/F/6M/130V/ELUME 6P	60	E26	130	Frost	C-9	6000	635	3 1/8	79	120
1 57626	60A19/CL/6M/130V/ELUME 6P	60	E26	130	Clear	C-9	6000	655	3 1/8	79	120
BR30											
52452	65BR30/FL/5M/ES/130V/ELUME 2P	65	E26	130	Frost	CC-6	5000	590	4	101	60
G16.5											
52453	25G16.5/CL/3M/E12/130V/ELUME 2P	25	E12	130	Clear	C-7A	3000	160	1 7/8	48	60
52454	40G16.5/CL/3M/E12/130V/ELUME 2P	40	E12	130	Clear	C-7A	3000	315	1 7/8	48	120
G25											
52455	40G25/CL/3M/130V/ELUME 2P	40	E26	130	Clear	C-9	3000	350	2 7/8	73	60
52457	40G25/WH/3M/130V/ELUME 2P	40	E26	130	White	C-9	3000	330	2 7/8	73	60
1 52456	60G25/CL/3M/130V/ELUME 2P	60	E26	130	Clear	C-9	3000	645	2 7/8	73	60
R16											
52459	40R16/SW/1M/120V/ELUME 2P	40	E26	120	Soft White	CC-6	1000	445	3 1/32	77	60
52460	60R16/SW/1M/130V/ELUME 2P	60	E26	130	Soft White	CC-6	1000	730	3 1/32	77	60
R20											
52462	30R20/FL/5M/130V/ELUME 2P	30	E26	130	Frost	C-9	5000	135	2 9/16	65	60
61707	45R20/FL/5M/130V/ELUME 2P	45	E26	130	Frost	CC-6	5000	242	2 9/16	65	45
1 52463	75R20/FL/5M/130V/ELUME 2P	75	E26	130	Frost	C-9/5	5000	540	2 9/16	65	60

¹This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted