



Ideal for commercial and institutional facilities, this luminaire's profile is less than 4' (48") deep with finished sides for clean, modern look. It's hinged door is equipped with rotary cam latches for easy maintenance. For use in indoor applications, these troffers made to be installed in T-grid applications. Drywall kits available and sold separately.

Pre-wired

For the complete definition of our abbreviated codes please consult our lexicon on page 24.



Order code	Description	Series	Type	Length x Width (ft.)	No. of lamps	Wattage/ Lamp type	Voltage (V)	Ballast	Ballast factor	Shielding
FRT/14/232/2ISN	FRT/14/232T8/2ISN/K12/TG/PW/STD	FR	T	14	2	32 W - T8	2	IS	N	K12
FRT/24/432/2ISN	FRT/24/432T8/2ISN/K12/TG/PW/STD	FR	T	24	4	32 W - T8	2	IS	N	K12
FRT/14/232/3ISN	FRT/14/232T8/3ISN/K12/TG/PW/STD	FR	T	14	2	32 W - T8	3	IS	N	K12
FRT/24/432/3ISN	FRT/24/432T8/3ISN/K12/TG/PW/STD	FR	T	24	4	32 W - T8	3	IS	N	K12

Note: Lamps not included.

Accessories

Order code	Description	Order code	Description
DWK/FRT/14	DRYWALL KIT FOR 1X4 FRT	DWK/FRT/24	DRYWALL KIT FOR 2X4 FRT

Fluorescent Recessed Troffer