

Product Details



Order Code: 11171

Product (Internal) Code: 6106HO

International Article Number (EAN/UPC): 46677381776

F96T12/DL/HO/O/RS/R17D

FLUORESCENT LINEAR HIGH OUTPUT (HO) T12 / REC. D.C. / RAPID START (RS) / 110W / 6500K

Product Group:	High Output (HO)
Starting Method:	Rapid Start (RS)
Watts (W):	110
Shape:	T12
Base:	Rec. D.C.
Average Life (Hours):	12000
Colour Temperature (K):	6500 (Daylight Deluxe)
Colour:	Daylight
Colour Rendering Index (CRI):	79
Nominal Length - IN (mm):	96 (2440)
Diameter (mm):	38
Initial Lumens:	7800
Brand:	Generic
Available Packaging Formats:	
EA	
1 CS = 15 EA	
1 PAL = 675 EA	