

Order code	Description	Watts (W)	Base	Volts (V)	Finish/Colour	Average life (hrs)	Filament	Lumens at 120 V (lm)	Case qty
A19									
MOL : 4 1/4 in. (108 mm) LCL : 3 1/4 in. (79 mm)									
† 50933	40A19/CL/1M/120V/STD/4P	(4 pack) 40	E26	120	Clear	1 000	C-9	320	120
† 50934	40A19/F/1M/120V/STD/4P	(4 pack) 40	E26	120	Frost	1 000	C-9	310	120
† 50025	40A19/CL/6M/130V/STD/2P	(2 pack) 40	E26	130	Clear	6 000	C-9	230	120
† 50029	40A19/F/6M/130V/STD/2P	(2 pack) 40	E26	130	Frost	6 000	C-9	220	120
† 50944	40A19/CL/6M/130V/STD/4P	(4 pack) 40	E26	130	Clear	6 000	C-9	230	120
† 50945	40A19/F/6M/130V/STD/4P	(4 pack) 40	E26	130	Frost	6 000	C-9	220	120
† 50935	60A19/CL/1M/120V/STD/4P	(4 pack) 60	E26	120	Clear	1 000	C-9	660	120
† 50026	60A19/CL/6M/130V/STD/2P	(2 pack) 60	E26	130	Clear	6 000	C-9	440	120
† 50946	60A19/CL/6M/130V/STD/4P	(4 pack) 60	E26	130	Clear	6 000	C-9	440	120
† 50936	60A19/F/1M/120V/STD/4P	(4 pack) 60	E26	120	Frost	1 000	C-9	640	120
† 50947	60A19/F/6M/130V/STD/4P	(4 pack) 60	E26	130	Frost	6 000	C-9	430	120
† 50039	60A19/F/6M/130V/STD/2P	(2 pack) 60	E26	130	Frost	6 000	C-9	430	120
† 50938	75A19/F/1M/120V/STD/4P	(4 pack) 75	E26	120	Frost	1 000	C-9	820	120
† 10362	75A19/F/6M/130V/STD/4P	(4 pack) 75	E26	130	Frost	6 000	C-9	480	120
† 10363	75A19/CL/6M/130V/STD/4P	(4 pack) 75	E26	130	Clear	6 000	C-9	490	120
† 50027	100A19/CL/6M/130V/STD/2P	(2 pack) 100	E26	130	Clear	6 000	C-9	700	120
A21									
MOL : 5 3/16 in. (135 mm) LCL : 3 7/32 in. (90 mm)									
† 50116	100A21/CL/5M/130V/STD	100	E26	130	Clear	5 000	C-9	780	120
† 50515	100A21/F/5M/130V/STD	100	E26	130	Frost	5 000	C-9	780	60
† 50481	150A21/F/5M/120V/STD	150	E26	120	Frost	5 000	C-9	1 700	120
† 50085	150A21/CL/5M/130V/STD	150	E26	130	Clear	5 000	C-9	1 250	60
† 50067	150A21/F/5M/130V/STD	150	E26	130	Frost	5 000	C-9	1 250	60
A23									
MOL : 6 3/16 in. (157 mm) LCL : 5 1/2 in. (128 mm)									
† 50163	100A23/CL/5M/130V/STD	100	E26	130	Clear	5 000	C-9	755	60
† 50070	150A23/F/5M/130V/STD	150	E26	130	Frost	5 000	C-9	1 250	60
† 50086	200A23/CL/5M/130V/STD	200	E26	130	Clear	5 000	C-9	1 815	60
† 50068	200A23/F/5M/130V/STD	200	E26	130	Frost	5 000	C-9	1 815	60
B8									
MOL : 3 3/32 in. (80 mm) LCL : 1 7/32 in. (48 mm)									
50635	15B8/CL/2.5M/E12/130V/STD	15	E12	130	Clear	2 500	C-7A	70	120
50638	15B8/F/2.5M/E12/130V/STD	15	E12	130	Frost	2 500	C-7A	70	120
50636	25B8/CL/2.5M/E12/130V/STD	25	E12	130	Clear	2 500	C-7A	150	120
50639	25B8/F/2.5M/E12/130V/STD	25	E12	130	Frost	2 500	C-7A	115	120
50637	40B8/CL/2.5M/E12/130V/STD	40	E12	130	Clear	2 500	CC-2V	235	120
50640	40B8/F/2.5M/E12/130V/STD	40	E12	130	Frost	2 500	CC-2V	230	120
50645	60B8/CL/2.5M/E12/130V/STD	60	E12	130	Clear	2 500	CC-2V	455	120
B10									
MOL : 3 29/32 in. (99 mm) LCL : 1 29/32 in. (45 mm)									
50611	15B10/CL/3M/E12/130V/STD	15	E12	130	Clear	3 000	C-7A	75	120
50543	25B10/CL/3M/E12/130V/STD	25	E12	130	Clear	3 000	CC-2V	165	120
50612	25B10/F/3M/E12/130V/STD	25	E12	130	Frost	3 000	CC-2V	165	120
MOL : 3 1/2 in. (89 mm) LCL : 2 1/4 in. (54 mm)									
10499	15B10/F/3M/130V/STD	15	E26	130	Frost	3 000	C-7A	70	500
50632	15B10/CL/3M/130V/STD	15	E26	130	Clear	3 000	C-7A	75	120
50621	25B10/CL/3M/130V/STD	25	E26	130	Clear	3 000	CC-2V	165	120
MOL : 3 29/32 in. (101 mm) LCL : 1 29/32 in. (45 mm)									
50548	25B10/CL/3M/E14/130V/STD	25	E14	130	Clear	3 000	CC-2V	165	120
50551	25B10/F/3M/E14/130V/STD	25	E14	130	Frost	3 000	CC-2V	195	500

† This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.

General Service Lamps