

Order code	Description	Watts (W)	Base	Volts (V)	Finish/ Colour	Average life (hrs)	Filament	Lumens at 120 V (lm)	Case qty
T6									
MOL : 3 1/16 in. (78 mm) LCL : 1 3/16 in. (40 mm)									
50667	15T6/CL/7.5M/E12/130V/STD	15	E12	130	Clear	7 500	C-5A	75	120
50668	15T6/CL/7.5M/E12/145V/STD	15	E12	145	Clear	7 500	C-5A	90	120
50675	15T6/CL/5M/E17/130V/STD	15	E17	130	Clear	5 000	C-5A	70	120
50676	15T6/CL/7.5M/E17/145V/STD	15	E17	145	Clear	7 500	C-5A	90	120
T6.5									
MOL : 5 13/32 in. (137 mm) LCL : 3 5/32 in. (80 mm)									
52127	7T6.5/CL/40M/ES/E12/145V/STD	7	E12	145	Clear	40 000	D	40	500
52128	7T6.5/CL/40M/ES/E17/145V/STD	7	E17	145	Clear	40 000	D	40	500
51052	20T6.5/CL/5M/BA15d/130V/STD	20	BA15d	130	Clear	5 000	C-8	115	500
50679	20T6.5/F/5M/BA15d/130V/STD	20	BA15d	130	Frost	5 000	C-8	115	120
50677	20T6.5/CL/5M/E17/130V/STD	20	E17	130	Clear	5 000	C-8	115	120
50678	20T6.5/F/5M/E17/130V/STD	20	E17	130	Frost	5 000	C-8	115	120
51056	25T6.5/CL/5M/BA15d/125V/STD	25	BA15d	125	Clear	5 000	C-8	180	500
50674	25T6.5/CL/7.5M/BA15d/145V/STD	25	BA15d	145	Clear	7 500	C-8	180	120
50729	25T6.5/F/7.5M/BA15d/145V/STD	25	BA15d	145	Frost	7 500	C-8	145	500
50671	25T6.5/CL/5M/E12/130V/STD	25	E12	130	Clear	5 000	C-8	135	120
50672	25T6.5/CL/7.5M/E12/145V/STD	25	E12	145	Clear	7 500	C-8	180	120
50669	25T6.5/CL/5M/E17/130V/STD	25	E17	130	Clear	5 000	C-8	135	120
50670	25T6.5/CL/7.5M/E17/145V/STD	25	E17	145	Clear	7 500	C-8	180	120
50673	25T6.5/F/7.5M/E17/145V/STD	25	E17	145	Frost	7 500	C-8	180	500
50680	40T6.5/CL/5M/E17/130V/STD	40	E17	130	Clear	5 000	C-8	280	120
52191	40T6.5/F/5M/E17/130V/STD	40	E17	130	Frost	5 000	C-8	210	500
T7									
MOL : 2 3/16 in. (59 mm) LCL : 1 3/16 in. (33 mm)									
52195	15T7/CL/1.5M/BA15d/120V/STD	15	BA15d	120	Clear	1 500	C-7A	100	1 000
52196	15T7/F/1.5M/BA15d/130V/STD	15	BA15d	130	Frost	1 500	C-7A	75	1 000
52192	15T7/CL/1.5M/E12/120V/STD	15	E12	120	Clear	1 500	C-7A	100	1 000
52194	15T7/CL/1.5M/E17/120V/STD	15	E17	120	Clear	1 500	C-7A	100	1 000
52201	25T7/CL/1.5M/E12/130V/STD	25	E12	130	Clear	1 500	C-7A	115	1 000
T8									
MOL : 2 9/16 in. (65 mm) LCL : 1 3/8 in. (41 mm)									
52198	25T8/CL/1.5M/BA15d/120V/STD	25	BA15d	120	Clear	1 500	C-7A	220	1 000
52199	25T8/F/1.5M/BA15d/130V/STD	25	BA15d	130	Frost	1 500	C-7A	160	1 000
52200	25T8/CL/1.5M/E12/120V/STD	25	E12	120	Clear	1 500	C-7A	220	1 000
52197	25T8/CL/1.5M/E17/120V/STD	25	E17	120	Clear	1 500	C-7A	220	1 000
T10									
MOL : 5 in. (127 mm) LCL : 2 3/4 in. (70 mm)									
50923	15T10/CL/3M/130V/STD	15	E26	130	Clear	3 000	C-5V	75	120
50924	15T10/F/3M/130V/STD	15	E26	130	Frost	3 000	C-5V	75	120
50925	25T10/CL/3M/130V/STD	25	E26	130	Clear	3 000	C-5V	135	120
50928	25T10/F/3M/130V/STD	25	E26	130	Frost	3 000	C-5V	135	120
50926	40T10/CL/3M/130V/STD	40	E26	130	Clear	3 000	C-5V	195	120
50929	40T10/F/3M/130V/STD	40	E26	130	Frost	3 000	C-5V	195	120
¹ 50927	60T10/CL/3M/130V/STD	60	E26	130	Clear	3 000	C-5V	365	120
¹ 50930	60T10/F/3M/130V/STD	60	E26	130	Frost	3 000	C-5V	365	120
T10 HO									
MOL : 5 13/32 in. (137 mm) LCL : 3 23/32 in. (85 mm)									
50164	15T10/CL/3M/HO/130V/STD	15	E26	130	Clear	3 000	C-8	70	120
50149	25T10/CL/3M/HO/130V/STD	25	E26	130	Clear	3 000	C-8	175	120
50131	25T10/F/3M/HO/130V/STD	25	E26	130	Frost	3 000	C-8	175	120
50129	40T10/CL/3M/HO/130V/STD	40	E26	130	Clear	3 000	C-8	300	120
50132	40T10/F/3M/HO/130V/STD	40	E26	130	Frost	3 000	C-8	300	120
¹ 50130	60T10/CL/3M/HO/130V/STD	60	E26	130	Clear	3 000	C-8	530	120
¹ 50133	60T10/F/3M/HO/130V/STD	60	E26	130	Frost	3 000	C-8	530	120

¹ This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.

General Service Lamps