

Miniature - Miniatures



Fig.1



Fig.2

3

Line Ligne	Lamp Shape Forme Lampe	Volts Tension	Amps (A) Watts Puiss. (W)	Lamp Base Culot Lampe	Internal Code Interne	Filament	Couleur Couleur	Avg. Life (Hrs) Vie moy. (Hres)	Lumens	MSCP	L.C.L. Inches - (mm) H.C.L. Pouces - (mm)	M.O.L. Inches - (mm) L.H.T.M. Pouces - (mm)	Diam. inches (mm) Pouces (mm)	Fig. # N° Fig.
------------	------------------------	---------------	---------------------------	-----------------------	-----------------------	----------	-----------------	---------------------------------	--------	------	---	---	-------------------------------	----------------

**B-3 1/2 Bulb
Lampe B-3 1/2**

1	B-3 1/2	1.9	0.6A	P13.5s	PR-8	C-2R		10		0.65	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
2	B-3 1/2	2.2	0.47A	P13.5s	KPR-104	C-2R		15			1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
3	B-3 1/2	2.33	0.27A	P13.5s	PR-4	C-2R		10		0.4	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
4	B-3 1/2	2.35	0.35A	P13.5s	PR-5	C-2R		35		0.45	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
5	B-3 1/2	2.38	0.5A	P13.5s	PR-2	C-2R		15		0.8	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
6	B-3 1/2	2.4	0.7A	P13.5s	PR-31	C-2R		20		1.3	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
7	B-3 1/2	2.4	0.7A	P13.5s	KPR-102	C-2R		15		1.3	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
8	B-3 1/2	2.4 2.4	0.50A / 0.50A	P13.5s	PR-14	C-2R / S-2		15		0.85 0.85	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
9	B-3 1/2	2.47	0.3A	P13.5s	PR-6	C-2R		30		0.45	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
10	B-3 1/2	2.7	0.15A	P13.5s	PR-9	C-2R		45		0.25	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
11	B-3 1/2	3	0.7A	P13.5s	395X	S-2		50		0.15	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
12	B-3 1/2	3.6	0.2A	P13.5s	PR-29	C-2R		30		0.6	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
13	B-3 1/2	3.6	0.7A	P13.5s	KPR-103	C-2R		15		2.71	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
14	B-3 1/2	3.7	0.3A	P13.5s	PR-7	C-2R		30		0.9	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
15	B-3 1/2	3.75	0.86A	P13.5s	PR-30	C-2R		40		2.25	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
16	B-3 1/2	4.75	0.5A	P13.5s	PR-13	C-2R		15		2.2	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
17	B-3 1/2	4.8	0.75A	P13.5s	KPR-113	C-2R		20		4.06	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
18	B-3 1/2	4.8	0.7A	P13.5s	PR-32	C-2R		20		3.3	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
19	B-3 1/2	4.82	0.5A	P13.5s	PR-15	C-2R		30		2	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
20	B-3 1/2	4.9	0.3A	P13.5s	PR-17	C-2R		30		1.2	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
21	B-3 1/2	5.95	0.5A	P13.5s	PR-12	C-2R		15		3	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
22	B-3 1/2	7.2	0.55A	P13.5s	PR-18	C-2R		3		4.2	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
23	B-3 1/2	8.63	0.5A	P13.5s	PR-20	C-2R		15		5	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1
24	B-3 1/2	12.5	0.25A	P13.5s	PR-16	C-2R		50		2.7	1/4 (6.35)	1 1/4 (31.8)	7/16 (11.3)	1

**B-6 Bulb
Lampe B-6**

25	B-6	4	1A	BA15d	BM30A	C-6		200		3.53	1 1/16 (27)	1 3/4 (44.4)	3/4 (19.8)	2
----	-----	---	----	-------	-------	-----	--	-----	--	------	-------------	--------------	------------	---