

# Fluorescent - Fluorescentes



Fig.8



Fig.9

9

Line Ligne	Internal Code Interne	Ordering Code Description Code Commande Description	Watts Puiss.	Lamp Shape Forme lampe	Colour Couleur	Lamp Base Culot Lampe	Colour Temp. Couleur (°K)	CRI IRC	Avg. Life (Hrs) Vie moy. (Hres)	Initial Lumens Initiaux	Diam. inches (mm) Pouces (mm)	Nominal Length Longueur nominale	Case Qty Qté Caisse	Fig. # N° Fig.
------------	-----------------------	---	--------------	------------------------	----------------	-----------------------	---------------------------	---------	---------------------------------	-------------------------	-------------------------------	----------------------------------	---------------------	----------------

### Rapid Start Fluorescent Lamps T12 Lampes fluorescentes à allumage rapide T12

246	605041K	F40T12/841/RS	40	T12		Med. Bi-Pin	4100	85	20000+	3300	1 1/2 (38)	48 (1220)	30	8
247	605050K	F40T12/850/RS	40	T12		Med. Bi-Pin	5000	85	20000+	3280	1 1/2 (38)	48 (1220)	30	8
248	605065K	F40T12/865K/RS	40	T12		Med. Bi-Pin	6500	80	20000+	3050	1 1/2 (38)	48 (1220)	30	8

### Slimline Fluorescent Lamps - Instant Start T12 Lampes fluorescentes fineline - allumage instanté T12

249	6108	F24T12/CW	21	T12	Cool White Blanc froid	Single Pin	4100	62	7500	1090	1 1/2 (38)	24 (610)	30	9
250	6110	F36T12/CW	30	T12	Cool White Blanc froid	Single Pin	4100	62	7500	1850	1 1/2 (38)	36 (915)	24	9
251	6050IS	F40T12/CW/IS	40	T12	Cool White Blanc froid	Med. Bi-Pin	4150	62	9000	3000	1 1/2 (38)	48 (1220)	30	8
252	6112	F42T12/CW	36	T12	Cool White Blanc froid	Single Pin	4100	62	7500	2200	1 1/2 (38)	42 (1067)	30	9
253	6102WW	F48T12/WW	39	T12	Warm White Blanc chaud	Single Pin	3000	53	9000	2950	1 1/2 (38)	48 (1220)	30	9
254	6102	F48T12/CW	40	T12	Cool White Blanc froid	Single Pin	4100	62	9000	2950	1 1/2 (38)	48 (1220)	15	9
255	6102D	F48T12/D	40	T12	Daylight Lumière du jour	Single Pin	6500	79	9000	2500	1 1/2 (38)	48 (1220)	30	9
256	6103	F60T12/CW	50	T12	Cool White Blanc froid	Single Pin	4100	62	12000	3450	1 1/2 (38)	60 (1524)	30	9
257	6103D	F60T12/D	50	T12	Daylight Lumière du jour	Single Pin	6500	79	12000	3150	1 1/2 (38)	60 (1524)	30	9
258	6104	F72T12/CW	50	T12	Cool White Blanc froid	Single Pin	4100	62	12000	4450	1 1/2 (38)	72 (1830)	15	9
259	6104D	F72T12/D	50	T12	Daylight Lumière du jour	Single Pin	6500	79	12000	3800	1 1/2 (38)	72 (1830)	15	9
260	6203	F64T12/CW	51	T12	Cool White Blanc froid	Single Pin	4100	62	12000	3750	1 1/2 (38)	64 (1626)	15	9
261	6203D	F64T12/D	51	T12	Daylight Lumière du jour	Single Pin	6500	79	12000	3200	1 1/2 (38)	64 (1626)	15	9
262	6306	F72T12/WW	55	T12	Warm White Blanc chaud	Single Pin	3000	53	12000	4450	1 1/2 (38)	72 (1830)	15	9
263	6105ES	F96T12/CW/ES	60	T12	Cool White Blanc froid	Single Pin	4100	62	12000	5400	1 1/2 (38)	96 (2240)	15	9
264	6105C50ES	F96T12/C50/ES	60	T12	Colour 50 Couleur 50	Single Pin	5000	92	12000	4100	1 1/2 (38)	96 (2240)	15	9
265	6106ES	F96T12/DX/ES	60	T12	Daylight Lumière du jour	Single Pin	6500	84	12000	4200	1 1/2 (38)	96 (2240)	15	9
266	6105LWES	F96T12/LW/ES	60	T12	Lite White Blanc Léger	Single Pin	4200	51	12000	5600	1 1/2 (38)	96 (2240)	15	9
267	6107ES	F96T12/WW/ES	60	T12	Warm White Blanc chaud	Single Pin	3000	53	12000	5500	1 1/2 (38)	96 (2240)	15	9