



Les images ne sont pas à l'échelle. Toutes les lampes sont claires à moins d'être autrement identifiées. **** Givrée

Code de commande	Description	Code de lampe	Forme	Culot	Tension (V)	Ampères (A)	Puissance (W)	Vie moyenne (h)	Diamètre (po) (mm)	HCL (po) (mm)	LHTM (po) (mm)	Qté paq.
R												
13073	20R12/FR/13V/ BA15S	1383	R-12	BA15s	13.00	1.538	20	300	1.55 39.26	S.O. S.O.	2.60 66.00	10
13076	20R12/F/28V/ BA15S ****	1385	R-12	BA15s	28.00	0.714	20	300	1.55 39.26	S.O. S.O.	2.60 66.00	10
13837	25RP11/CL/12V/ BA15D/STD	EMR-1125	RP-11	BA15d	12.00	2.083	25	75	1.42 36.10	1.30 33.00	2.24 57.00	10
S												
50305	6S6/CL/6V/BA15D/STD	S.O.	S-6	BA15d	6.00	1.000	6	1500	0.78 19.81	1.00 25.40	1.89 48.00	10
50302	6S6/CL/24V/BA15D/STD	S.O.	S-6	BA15d	24.00	0.250	6	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50304	6S6/CL/32V/BA15D/STD	S.O.	S-6	BA15d	32.00	0.188	6	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50291	6S6/CL/125V/BA15d/STD	S.O.	S-6	BA15d	125.00	0.048	6	3000	0.78 19.81	1.19 30.20	1.89 48.00	10
50285	10S6/CL/125V/BA15d/STD	S.O.	S-6	BA15d	125.00	0.080	10	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50295	6S6/CL/130V/BA15d/STD	S.O.	S-6	BA15d	130.00	0.046	6	3000	0.78 19.81	1.19 30.20	1.89 48.00	10
50297	6S6/CL/145V/BA15d/STD	S.O.	S-6	BA15d	145.00	0.041	6	3000	0.78 19.81	1.19 30.20	1.89 48.00	10
51145	10S6/CL/230V/BA15d/STD	S.O.	S-6	BA15d	230.00	0.043	10	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50292	6S6/CL/12V/E12/STD	S.O.	S-6	E12	12.00	0.500	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50301	6S6/CL/24V/E12/STD	S.O.	S-6	E12	24.00	0.250	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50303	6S6/CL/32V/E12/STD	S.O.	S-6	E12	32.00	0.188	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50306	6S6/CL/75V/E12/STD	S.O.	S-6	E12	75.00	0.080	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50287	3S6/CL/125V/E12/STD	S.O.	S-6	E12	125.00	0.024	3	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50290	6S6/CL/125V/E12/STD	S.O.	S-6	E12	125.00	0.048	6	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50284	10S6/CL/125V/E12/STD	S.O.	S-6	E12	125.00	0.080	10	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
52119	15S6/CL/125V/E12/STD	S.O.	S-6	E12	125.00	0.120	15	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50288	3S6/CL/130V/E12/STD	S.O.	S-6	E12	130.00	0.023	3	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50294	6S6/CL/130V/E12/STD	S.O.	S-6	E12	130.00	0.046	6	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50296	6S6/CL/145V/E12/STD	S.O.	S-6	E12	145.00	0.041	6	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50299	6S6/CL/230V/E12/STD	S.O.	S-6	E12	230.00	0.026	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50286	10S6/CL/230V/E12/STD	S.O.	S-6	E12	230.00	0.043	10	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50534	6S6/CL/120V/E17/STD	S.O.	S-6	E17	120.00	0.050	6	1500	0.78 19.81	1.46 37.00	1.81 46.00	10
50324	9S8/CL/6V/BA15D/STD	EMS-0509	S-8	BA15d	6.00	1.500	9	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50323	9S8/CL/12V/BA15D/STD	EMS-1109	S-8	BA15d	12.00	0.750	9	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50918	S8/CL/12.8V/1.04A/BA15d/STD	94	S-8	BA15d	12.80	1.040	13	700	1.00 25.40	1.13 28.60	2.01 51.00	10
50413	S8/CL/12.8V/1.44A/BA15d/STD	1142	S-8	BA15d	12.80	1.440	18	1000	1.00 25.40	1.25 31.80	2.01 51.00	10
50321	9S8/CL/24V/ BA15D/STD	EMS-2209	S-8	BA15d	24.00	0.375	9	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50319	18S8/CL/24V/ BA15D/STD	EMS-2218	S-8	BA15d	24.00	0.750	18	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50426	S8/CL/28V/0.93 0.34A/DCI/STD	1662	S-8	BAY15d	28.00	0.340	10	1000	1.00 25.40	1.25 31.80	2.01 51.00	10
13040	S8/CL/28V/0.71A/BA15D	1204	S-8	BA15d	28.00	0.710	20	400	1.00 25.40	1.25 31.80	2.01 51.00	10
22119	S8/CL/28V/1.02A/BA15D/STD	1638	S-8	BA15d	28.00	1.020	29	500	1.00 25.40	1.25 31.80	2.01 51.00	10
22073	S8/CL/32V/0.45A/BA15D/STD	1228	S-8	BA15d	32.00	0.450	14	150	1.00 25.40	1.13 28.60	2.01 51.00	10
50690	S8/CL/40V/0.38A/BA15d/STD	1229	S-8	BA15d	40.00	0.380	15	400	1.00 25.40	1.13 28.60	2.01 51.00	10

Cette liste ne comporte qu'une portion de la sélection de lampes miniatures disponibles chez STANDARD. Visitez notre site web pour consulter la sélection complète à www.standardpro.com