



Code de commande	Description	Base	Volts (V)	Watts (W)
38053	B15D (DC) ENTR ARRIERE/FILS 6"	BA15d	240	1 000
38047	E11(MC)MONTAGE ARRIERE FILS 6"	E11	250	1 000
38048	E11(MC) ENTREE ARRIERE FILS 6"	E11	300	500
38201	J-12D CULOT E11 MONTURE 12" FILS INFER	E11	250	1 000
38042	E17(INT) FILS 6"	E17	250	500
38051	G4 ENTREE ARRIERE FILS 6"	G4	24	100
38238	G4 BACK ENTRY 24" FILS	G4	25	100
38046	G6.35(G1+G2) ENTR ARR FILS 6"	G5.3-GX5.3	300	500
38000	GU10 BACK ENTRY 18" LEADS	GU10	250	500
62187	DF-05 GU-10/GZ-10 BASE (TAL) LAMPHOLDER	GU10	250	1 000
38043	PAR CONNECTOR MOGUL END PRONG	GX16d	125	1 000
38045	GX5.3 (MR16) ENTR ARR FILS 6"	GX5.3	250	1 000
38049	GX5.3(MR16) ENTR COTE FILS 24"	GX5.3	24	100
11677	SOCKET FOR HFE-J0500-F EURO FL	N/A	N/A	N/A
38054	RSC SUPPORT (UN BOUT)	R7s	250	1 000
38055	RSC 199MM SUPPORT (DEUX BOUTS)	R7s	250	1 000
38056	RSC 79MM SUPPORT (DEUX BOUTS)	R7s	250	500
38199	J-1 CULOT RSC R-7s	R7s	600	1 500
10717	RAL2/HOLDERSET/S14S	S14s	250	N/A