

Code de commande	Description		Watts (W)	Culot	Volts (V)	Finition/ Couleur	Vie moyenne (h)	Filament	Lumens à 120 V (lm)	Qté boîte
A19										
LHTM : 4 1/4 po (108 mm)			HCL : 3 3/8 po (79 mm)							
† 50933	40A19/CL/1M/120V/STD/4P	(Paq. 4)	40	E26	120	Claire	1 000	C-9	320	120
† 50934	40A19/F/1M/120V/STD/4P	(Paq. 4)	40	E26	120	Givrée	1 000	C-9	310	120
† 50025	40A19/CL/6M/130V/STD/2P	(Paq. 2)	40	E26	130	Claire	6 000	C-9	230	120
† 50029	40A19/F/6M/130V/STD/2P	(Paq. 2)	40	E26	130	Givrée	6 000	C-9	220	120
† 50944	40A19/CL/6M/130V/STD/4P	(Paq. 4)	40	E26	130	Claire	6 000	C-9	230	120
† 50945	40A19/F/6M/130V/STD/4P	(Paq. 4)	40	E26	130	Givrée	6 000	C-9	220	120
† 50935	60A19/CL/1M/120V/STD/4P	(Paq. 4)	60	E26	120	Claire	1 000	C-9	660	120
† 50026	60A19/CL/6M/130V/STD/2P	(Paq. 2)	60	E26	130	Claire	6 000	C-9	440	120
† 50946	60A19/CL/6M/130V/STD/4P	(Paq. 4)	60	E26	130	Claire	6 000	C-9	440	120
† 50936	60A19/F/1M/120V/STD/4P	(Paq. 4)	60	E26	120	Givrée	1 000	C-9	640	120
† 50947	60A19/F/6M/130V/STD/4P	(Paq. 4)	60	E26	130	Givrée	6 000	C-9	430	120
† 50039	60A19/F/6M/130V/STD/2P	(Paq. 2)	60	E26	130	Givrée	6 000	C-9	430	120
† 50938	75A19/F/1M/120V/STD/4P	(Paq. 4)	75	E26	120	Givrée	1 000	C-9	820	120
† 10362	75A19/F/6M/130V/STD/4P	(Paq. 4)	75	E26	130	Givrée	6 000	C-9	480	120
† 10363	75A19/CL/6M/130V/STD/4P	(Paq. 4)	75	E26	130	Claire	6 000	C-9	490	120
† 50027	100A19/CL/6M/130V/STD/2P	(Paq. 2)	100	E26	130	Claire	6 000	C-9	700	120
A21										
LHTM : 5 3/16 po (135 mm)			HCL : 3 7/32 po (90 mm)							
† 50116	100A21/CL/5M/130V/STD		100	E26	130	Claire	5 000	C-9	780	120
† 50515	100A21/F/5M/130V/STD		100	E26	130	Givrée	5 000	C-9	780	60
† 50481	150A21/F/5M/120V/STD		150	E26	120	Givrée	5 000	C-9	1 700	120
† 50085	150A21/CL/5M/130V/STD		150	E26	130	Claire	5 000	C-9	1 250	60
† 50067	150A21/F/5M/130V/STD		150	E26	130	Givrée	5 000	C-9	1 250	60
A23										
LHTM : 6 3/16 po (157 mm)			HCL : 5 1/32 po (128 mm)							
† 50163	100A23/CL/5M/130V/STD		100	E26	130	Claire	5 000	C-9	755	60
† 50070	150A23/F/5M/130V/STD		150	E26	130	Givrée	5 000	C-9	1 250	60
† 50086	200A23/CL/5M/130V/STD		200	E26	130	Claire	5 000	C-9	1 815	60
† 50068	200A23/F/5M/130V/STD		200	E26	130	Givrée	5 000	C-9	1 815	60
B8										
LHTM : 3 3/32 po (80 mm)			HCL : 1 3/4 po (48 mm)							
50635	15B8/CL/2.5M/E12/130V/STD		15	E12	130	Claire	2 500	C-7A	70	120
50638	15B8/F/2.5M/E12/130V/STD		15	E12	130	Givrée	2 500	C-7A	70	120
50636	25B8/CL/2.5M/E12/130V/STD		25	E12	130	Claire	2 500	C-7A	150	120
50639	25B8/F/2.5M/E12/130V/STD		25	E12	130	Givrée	2 500	C-7A	115	120
50637	40B8/CL/2.5M/E12/130V/STD		40	E12	130	Claire	2 500	CC-2V	235	120
50640	40B8/F/2.5M/E12/130V/STD		40	E12	130	Givrée	2 500	CC-2V	230	120
50645	60B8/CL/2.5M/E12/130V/STD		60	E12	130	Claire	2 500	CC-2V	455	120
B10										
LHTM : 3 29/32 po (99 mm)			HCL : 1 29/32 po (45 mm)							
50611	15B10/CL/3M/E12/130V/STD		15	E12	130	Claire	3 000	C-7A	75	120
50543	25B10/CL/3M/E12/130V/STD		25	E12	130	Claire	3 000	CC-2V	165	120
50612	25B10/F/3M/E12/130V/STD		25	E12	130	Givrée	3 000	CC-2V	165	120
LHTM : 3 1/2 po (89 mm)			HCL : 2 1/4 po (54 mm)							
10499	15B10/F/3M/130V/STD		15	E26	130	Givrée	3 000	C-7A	70	500
50632	15B10/CL/3M/130V/STD		15	E26	130	Claire	3 000	C-7A	75	120
50621	25B10/CL/3M/130V/STD		25	E26	130	Claire	3 000	CC-2V	165	120
LHTM : 3 29/32 po (101 mm)			HCL : 1 29/32 po (45 mm)							
50548	25B10/CL/3M/E14/130V/STD		25	E14	130	Claire	3 000	CC-2V	165	120
50551	25B10/F/3M/E14/130V/STD		25	E14	130	Givrée	3 000	CC-2V	195	500

†Cet item n'est plus produit conformément à la loi sur les standards en matière d'efficacité énergétique, il sera disponible jusqu'à épuisement des stocks.

Lampes-réflecteurs d'usage général