

## **INDUSTRIAL CEILING FAN CONTROLS**



MC15



## **MC CEILING FAN SPEED CONTROLS**

- MC controls are available in 4 models: MC-3 (3 amp), MC-5 (5 amp), MC-10 (10 amp) and MC-15 (15 amp).
- MC15 can operate up to 12 fans on a single control.
- Infinite speed adjustment.
- Minimum speed adjustment screw.
- · All controls are designed to fit a standard electrical box.
- Mount in a dry location such as the control room.

PART #	MODEL	MAX # OF FANS PER CONTROL	VARIABLE SPEED OPERATION	POWER SUPPLY	AMPERAGE RATING	Shipping Weight
CN5041	MC-3	2	MANUAL	120V/1/60HZ	2.5	0.25 lbs
CN5061	MC-5	4	MANUAL	120V/1/60HZ	5	0.25 lbs
CN5101	MC-10	8	MANUAL	120V/1/60HZ	10	0.77 lbs
CN5151	MC-15	12	MANUAL	120V/1/60HZ	15	0.77 lbs
CN5061-230*	MC5-230	Check Fan Amperage	MANUAL	230V/1/60HZ	5	0.25 lbs

\*NOTE: Not for use with Industrial Ceiling Fans

## **FRMC5 CEILING FAN CONTROL**

- 5 amp rating for use with the Forward/Reverse Industrial Ceiling Fan models.
- Up to 4 fans can operate on a single control.
- A forward and reverse slide switch is provided to change the direction of the fan from updraft to downdraft.
- Infinite speed adjustment.
- Minimum speed adjustment.
- · All controls are designed to fit a standard electrical box.
- Mount in a dry location such as the control room.

PART #	MODEL	MAX # OF FANS/CONTROL	VARIABLE SPEED OPERATION	POWER SUPPLY	AMPERAGE RATING	SHIPPING WEIGHT
CNFRMC5	FRMC5	4	MANUAL C/W FORWARD/REVERSE SWITCH	120V/1/60HZ	5	0.35 lbs



## **CQ004 - QUIET SPEED CONTROL**

- Preferred control for areas where quiet operation is required (ie. churches).
- Control can operate one fan.
- Speeds Off/High/Medium/Low.
- · Control is designed to fit a standard wall switch box.
- Mount in a dry location such as the control room.

PART #	MODEL	MAX # OF FANS/CONTROL	VARIABLE SPEED OPERATION	POWER SUPPLY	AMPERAGE RATING	SHIPPING WEIGHT
CQ004	CQ004	1	OFF / HIGH / MEDIUM / LOW	120V/1/60HZ	1.25	0.25 lbs