

LED DISK LIGHT

part # LED-SM4D-WT-C

CANARM LTD.

PO Box 367, 2157 Parkedale Avenue, Brockville, Ontario K6V5V6
Tel: 613-342-5424 | Fax: 1-800-263-4598

2555 Rue Bernard Lefebvre, Laval, Quebec H7C 0A5
Tel: 1-450-665-2535 | Fax: 1-450-665-1910

808 Commerce Park Drive, Ogdensburg, New York, USA 13669
Tel: 1-800-267-4427 | Fax: 1-800-263-4598

www.canarm.com

General

Size of fixture: 5.9" W x 1.26" H x 5.9" D
 Finish: 4" white trim, frosted diffuser
 Lamp base: E26 adaptable, quick connectors
 Energy used: 12 watt
 Low Voltage
 Light output: 900 lumens
 Colour temperature: 3000K, warm white
 Dimmable using LEVITON #6633, LEVITON #6672 or LUTRON
 #CTCL-153PD dimmer.
 Bulb life: 50,000 hours
 Mounting: flush mount.
 Suitable for wet locations. Indoor/Outdoor enclosed use.
 Minimum -25 degree



Packaging

Color box: 6.69" x 6.69" x 2.36" (170 x 170 x 60mm)
 Weight: 1.10 lbs
 Master box: 26.18" x 14.37" x 7.68" (665 x 365 x 195mm)
 Pieces per master: 20
 Weight: 23.81 lbs

Warranty & Safety Standards

Warranty: 5 year
 cETLus rated
 Energy Star Rated
 GreenChoice
 Intergrated LED

Prepared for
Contact
Date
Presented by
Remarks