

**CANARM LTD.**

PO Box 367, 2157 Parkedale Avenue, Brockville, Ontario K6V5V6  
Tel: 613-342-5424 | Fax: 1-800-263-4598

2555 Rue Bernard Lefebvre, Laval, Quebec H7C 0A5  
Tel: 1-450-665-2535 | Fax: 1-450-665-1910

808 Commerce Park Drive, Ogdensburg, New York, USA 13669  
Tel: 1-800-267-4427 | Fax: 1-800-263-4598

www.canarm.com

# LED DISK LIGHT

## Flush mount Twin pack

### part # LED-SM4DL-WT-C2

**General**

Size of fixture: 5.9" W x 1.26" H x 5.9" D  
 Finish: 4" white trim, PC lens  
 Voltage: 120V  
 LED 10W  
 CRI 80  
 Light output: 660 lumens  
 Colour temperature: 3000K, warm white without 20W driver  
 Dimmable using LEVITON #6633, LEVITON #6672 dimmer.  
 Bulb life: 35,000 hours  
 Mounting: surface mount to standard outlet box  
 Suitable for wet locations. Indoor/Outdoor enclosed use.  
 Minimum -20 degrees

**Packaging**

Color box: 6.69" x 5.91" x 2.52" (170 x 150 x 65mm)  
 Weight: 2.21lbs  
 Master box: 27.56" x 14.17" x 7.09" (700 x 365 x 180mm)  
 Pieces per master: 10  
 Weight: 23.15 lbs

**Warranty & Safety Standards**

Warranty: 5 year  
 Intergrated LED  
 cETLus rated  
 Engery Star Rated  
 GreenChoice



<b>Prepared for</b>
<b>Contact</b>
<b>Date</b>
<b>Presented by</b>
<b>Remarks</b>