

SAK Series, Accessories
Q 10 SAK2.5**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

This type of cross-connection has a pre-assembled captive cross-connection lug, cross-connection sleeve and fixing screw.

All the individual parts are available separately on request. During installation, the pre-assembled cross-connectors are simply placed in the cross-connection slot in the middle of the terminal and screwed tight.

General ordering data

Order No.	0368700000
Type	Q 10 SAK2.5
Version	SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 10
GTIN (EAN)	4008190107796
Qty.	20 pc(s).

SAK Series, Accessories
Q 10 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	6 mm	Width	60.6 mm
Net weight	17.5 g		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	for cross-connection link		

Rated data

Rated voltage	0 V	Rated current	24 A
---------------	-----	---------------	------

Material data

Colour	Grey
--------	------

System specifications

Product family	SAK Series, Accessories
----------------	-------------------------

Classifications

ETIM 2.0	EC000489	ETIM 3.0	EC000489
UNSPSC	30-21-18-01	eClass 4.1	27-14-11-99
eClass 5.1	27-14-11-40	eClass 6.0	27-14-11-40
eClass 7.0	27-14-11-40		

Product information

Descriptive text technical data	Current-carrying capacity up to 41 A via the cross-connection, max. 6 mm ²
---------------------------------	---

Approvals

Approvals

