

fan control with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- 3 quiet fan speeds for increased comfort
- designed to reduce motor hum
- for use with only one ceiling paddle fan

quiet 3-speed control

single pole	1.5A	FSQ-2F-
-------------	------	----------------

replacement knobs



- standard knob
- quiet, 3-speed fan control knobs

knobs

standard knob	RK-
3-speed fan control knob, white	280-324-01
3-speed fan control knob, ivory	280-324-06

fan controls with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- for use with multiple ceiling paddle fans or exhaust fans

fully variable control

single pole fan control	5A	FS-5F-
factory set minimum speed		
single pole fan control	5A	FS-5E-
user adjustable minimum speed		




See page 101 for available colors.
To order, add color suffix to model number.
Example: **FSQ-2F- WH**





Shown actual size: Rotary dimmer and 1-gang Fassada® wallplate in ivory (IV)

available models

source type

-  incandescent/halogen lighting
-  quiet 3-speed fan controls
-  fully variable fan controls

control locations

-  single pole (one location)
-  3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

- WH** white
- IV** ivory

Rotary dimmers

product family features

- easy-turn knob adjusts light to your favorite level
- coordinating Fassada® wallplates available separately (including matte, gloss, and stainless steel finishes)
- **eco-dim**® model available