

**Fan control and fan/light control
model numbers**

 **Fan controls**

Digital fan controls—quiet 7-speed

Multi-location	MA-FQ4FM- CC ¹
120V, up to 4 canopy modules (1 A each)	

Multi-location package	MA-FQ3- CC ¹
120V, up to 4 canopy modules (1 A each)	

All above include one wall-mounted fan control and one fan-mounted canopy module. Wallplates sold separately.

Multi-location package (MA-FQ3-) also includes companion fan control (MA-AFQ4). Wallplates sold separately.

No derating required if ganged.

Canopy modules (fan-mounted)

Canopy module	CM-FQ1
120V 1 A	

All Maestro fan controls and fan/light controls include one canopy module for control of one fan. One additional canopy module (CM-FQ1) required for each additional fan—up to one fan total.

 **Fan/light controls**

Fan/light control—quiet 7-speed

Single-pole	MA-LFQHW- CC ³
120V 300W light (top)	

Incandescent/halogen	
1 canopy module for up to 1 A fan (bottom)	

Multi-location	MA-LFQM- CC ¹
120V 300W light (top)	

Incandescent/halogen	
1 canopy module for up to 1 A fan (bottom)	

All above include the necessary wall-mounted fan/light control and one fan-mounted canopy module.

Single-pole model includes wallplate.

Multi-location model may be used with up to two companion fan/light controls (MA-ALFQ35-), see pg. 66. Wallplates sold separately.

No derating required if ganged.

CC¹: Gloss and Satin color codes, see pg. 47
(Wallplates not included with above, order separately, see pg. 160)

CC³: Gloss color codes, see pg. 47

All models must be derated if ganged unless otherwise noted, see pg. 170.