

Dimmers and switches

Digital fade dimmers



- Tap on to favorite level; tap off
- Tap twice for full on
- Press, hold and release for delayed fade-to-off
- Touch rocker to adjust light level
- Provides true dimming from each location (with companion dimmers)
- **eco-dim®** model guarantees at least 15% energy savings compared to a standard switch
- **eco-minder™** green LED demonstrates 15% or more energy savings compared to a standard switch
- Dimmer advanced programming features available



eco-minder™

Digital switches



- For multi-location switching, use one Maestro multi-location switch with Maestro companion switches
- Tap switch on/off

Timers

Countdown timer switches (5–60 minutes/full on)



- Use with exhaust fans to reduce moisture, mold and mildew in bathrooms and kitchens
- Use with lighting
- Tap on to start timer; tap off
- Tap twice for untimed on
- Touch rocker to adjust countdown time
- One minute warning before lights/fan go off
- Top LED is full on with no timer action
- Timer advanced programming features available
- Multi-location control with companion switch

Countdown eco-timer switch (30 minutes)



- Use with exhaust fans to reduce moisture, mold and mildew in bathrooms and kitchens
- Use with lighting
- Tap on to start timer; tap off
- Touch rocker to adjust countdown time
- One minute warning before lights/fan go off
- **Timer always turns off**
- Single-location only
- Timer advanced programming features available

Switch model numbers

Switches

Digital switches

Multi-location/single-pole* MA-S8AM-**CC**³
120V 8A light or 3A fan

Multi-location/single-pole* MSC-S8AM-**CC**⁴
120V 8A light or 3A fan

Rated for: incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, general purpose fans and most non-dim LED drivers.

Multi-location/single-pole* MSCF-S6AM-277-**CC**⁴
277V 6A light

Multi-location/single-pole* MAF-S6AM-277-**CC**³
277V 6A light

Rated for: incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts and most non-dim LED drivers.

Timer model numbers

Timers

Countdown timer control switch (5–60 minutes/full on)**

Single-pole, no neutral required MA-T51-**CC**¹
120V 600W/VA (5A) on/off lighting load
(incandescent/halogen, MLV)
OR 3A general purpose fan(s)

Multi-location/single-pole* MA-T51MN-**CC**¹
120V 600W/VA (5A) on/off lighting load
(incandescent/halogen, MLV, ELV, fluorescent)
OR 3A general purpose fan(s)

Use MA-T51MN- with a companion switch (MA-AS- or MSC-AS-) for multi-location switching.

Countdown eco-timer control switch (30 minutes/full on)**

Single-pole MA-T530G-**EE**²
120V 600W/VA (5A) on/off lighting load
(incandescent/halogen, MLV)
OR 3A general purpose fan(s)

CC¹: Gloss and Satin color codes, see pg. 47

CC³: Gloss color codes, see pg. 47

CC⁴: Satin color codes, see pg. 47

EE²: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA)

(Wallplates not included with above, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

***Requires neutral wire connection.**

**Minimum load is 40W/VA.