

Available finishes

Use **BOLD** color code in model number (Example: SPS-5WC-**IV**)

Gloss finishes*



WH
White



LA
Light Almond



AL
Almond



IV
Ivory



GR
Gray



BR
Brown



BL
Black



SS
Stainless Steel

*Coordinating wallplates only available separately. For wallplate information, see pg. 160.

Stainless Steel wallplate includes black plastic trim/adaptor, visible from side. Match with separate Black (BL) controls.

Master controls

Wall mounted master controls



- Controls up to four dimmers of all load types
- 4-preset scenes, plus full on and all off
- Rocker for raise/lower master override
- IR receiver for remote control
- When using 120V and 277V products in the same backbox, use 600V rated cable. Follow NEC®, see application note #133 (U.S. requirements for mixing 120V and 277V products in the same Wallbox) visit www.lutron.com/applicationnotes

Wall mounted master controls with IR blasters



- Same features as above
- Controls up to four dimmers per blaster
- Requires two travel wires between master control and IR blasters



Dimmers and switches

Dimmers with IR receiver



- Tap on to favorite level; tap off
- Touch rocker to adjust light level
- Tap twice for full on
- Press, hold and release for delayed fade-to-off
- Provides true dimming from each location with companion dimmers

Plug-in lamp dimmers with integral IR receiver



- For use with table and floor lamps only
- Requires no wiring or tools
- Only available in Royal Plum (RP)

Digital switches



- For multi-location Spacer System multi-location switch with Spacer System companion switches
- When using 120V and 277V products in the same backbox, use 600V rated cable. Follow NEC®, see application note #133 (U.S. requirements for mixing 120V and 277V products in the same Wallbox) visit www.lutron.com/applicationnotes

Master control and dimmer model numbers

Master controls*

5-scene wall mounted master control

120V	SPS-5WC- CC ³
------	---------------------------------

Remote 5-scene wall mounted master control with two IR blasters

120V	SPS-5WCR- CC ³
------	----------------------------------

SPS-5WC- must be ganged in the same continuous backbox with Spacer System dimmers; its IR signal travels within the backbox to four dimmers in either direction. Remote-mounted SPS-5WCR- talks to Spacer System dimmers via IR blasters clip to the dimmer backbox and emit IR signals for up to two dimmers in either direction.

 **Incandescent/halogen dimmers**

Dimmers with IR receiver**

Single-location	SPS-600- CC ³
-----------------	---------------------------------

120V 600W

Single-location	SPS-1000- CC ³
-----------------	----------------------------------

120V 1000W

Multi-location	SPS-600M- CC ³
----------------	----------------------------------

120V 600W

Multi-location	SPS-1000M- CC ³
----------------	-----------------------------------

120V 1000W

Dimmers with IR receiver and a wallplate**

Single-pole	SPSW-600H- CC ³
-------------	-----------------------------------

120V 600W

Multi-location	SPSW-603H- CC ³
----------------	-----------------------------------

120V 600W

Dimmer, IR remote control, companion dimmer and wallplate**

Single-pole	SPSW-600-HTH- CC ³
-------------	--------------------------------------

120V 600W

Multi-location	SPSW-603-HTH- CC ³
----------------	--------------------------------------

120V 600W

Plug-in lamp dimmer model numbers

 **Plug-in lamp dimmers**

Plug-in lamp dimmer with integral IR receiver

Single-pole	SPS-300LD-RP
-------------	--------------

120V 300W

Plug-in lamp dimmer with IR remote control

Single-pole	SPS-300LD-HTH-RP
-------------	------------------

120V 300W

Plug-in lamp dimmer with IR receiver are available in Royal Plum (RP) only.

CC³: Gloss color codes, see pg. 77 (Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

*Requires neutral wire connection.

**Minimum load 60W/VA.