

# Farm Duty / Agriculture, High Torque

## Single Phase, TEFC

### Features:

- Ball bearings, shaft end mechanically locked on C-face models (excludes 5K models)
- 1.15 Service Factor (except as noted)
- Capacitor start design for high starting torque
- Capacitor start/capacitor run design for higher efficiency, as noted
- Low temperature manual reset thermal protector
- Totally enclosed and fully gasketed construction for dirty environments
- Condensate drains
- Shaft slinger
- UL Recognized and CSA Certified



### Rigid Base

HP	RPM	VOLTS	FRAME	CAT. NO.	MODEL NO.	STOCK	LIST PRICE	MULT. SYMB.	F.L. AMPS	WEIGHT	"C" DIM.	FOOT NOTES
1/3	1800	115/230	56	F13E1	5KC42GN0051Y	✓	\$286	F1	7.8/3.9	22	11.00	d
	1800	115/208-230	56	F101	56C17F5324	✓	\$286	F1	6.6/3.1-3.3	24	11.82	
1/2	1800	115/208-230	56	F12E1	5KC46GN0050Y	✓	\$327	F1	9.0/4.5-4.5	21	11.83	d
	1800	115/208-230	56	F102	56C17F5325	✓	\$327	F1	8.8/4.2-4.4	25	11.82	
3/4	1800	115/230	56	F34E1	5KC46PN0062Y	✓	\$390	F1	11.0/5.5	31	11.83	d,17
	1800	115/208-230	56	F103	56C17F5326	✓	\$390	F1	11.0/5.4-5.5	29	12.32	
1	1800	115/208-230	143T	Z123	143TCFR5328	✓	\$452	S1	13.4/6.8-6.7	31	12.87	
	1800	115/230	56	F10E1	5KC49TN0063Y	✓	\$425	F1	13.2/6.6	37	12.96	d,17
	1800	115/208-230	56	F104	56C17F5327	✓	\$425	F1	13.4/6.8-6.7	31	12.82	
1 1/2	1800	115/208-230	145T	F15E1	5KCR48WN0292Y		\$532	S1	14.5/7.1-7.3	44	14.07	ES,1
	1800	115/208-230	145T	Z118	145TBFR5328	✓	\$532	S1	15.2/8.2-7.6	40	13.87	1
	1800	115/208-230	56H	F100	5KCR48WN0273Y	✓	\$522	F1	14.5/7.1-7.3	44	13.82	d,ES,1
	1800	115/208-230	56H	F105	56B17F5307	✓	\$522	F1	15.2/8.2-7.6	41	13.82	ES,1
2	1800	115/230	145T	Z128	145TBFR5341	✓	\$591	S1	18.8/9.4	49	14.87	1
	1800	208-230	145T	C1904	5KCR49ZN0564Y	✓	\$591	S1	9.2	49	14.63	d,1,17
	1800	115/230	182T	Z119A	182TCFW7072	✓	\$644	S1	24.0/12.0	66	14.46	13
3	1800	230	184T	Z120A	184TBFW17045	✓	\$802	S1	14.2	92	14.96	1,13
5	1800	230	184T	Z121A	184TBFW7737	✓	\$976	S1	19.5	103	17.45	1,13
7 1/2	1800	230	215T	Z122	215TBFW7029	✓	\$1,448	S1	30.0	138	21.48	1

FARM DUTY / AGRICULTURAL

### C-Face Footed (Rigid Base)

HP	RPM	VOLTS	FRAME	CAT. NO.	MODEL NO.	STOCK	LIST PRICE	MULT. SYMB.	F.L. AMPS	WEIGHT	"C" DIM.	FOOT NOTES
1/3	1800	115/208-230	56C	F131	56C17F5358	✓	\$349	F1	6.6/3.1-3.3	23	11.82	
1/2	1800	115/208-230	56C	F132	56C17F5912	✓	\$390	F1	8.8/4.2-4.4	25	11.82	
3/4	1800	115/208-230	56C	F133	56C17F5913	✓	\$454	F1	11.5/4.5-5.5	29	12.32	
1	1800	115/208-230	56C	F134	56C17F5914	✓	\$488	F1	13.4/6.8-6.7	31	12.82	
1 1/2	1800	115/208-230	56HC	F135	56B17F5584	✓	\$586	F1	15.2/8.2-7.6	41	13.82	1,5
2	1800	115/230	56HC	K319	56B17F5319	✓	\$601	F1	18.8/9.4	50	14.82	1,5
3	1800	230	184TC	I314A	184TBFW7041	✓	\$901	S1	12.8	86	14.96	1,13
5	1800	230	184TC	I315A	184TBFW7034	✓	\$1,075	S1	19.5	101	17.45	1,13

