

Specifications

Lamp Wattage / Type

T4 Replaceable Fluorescent lamp

· Built-in Silent Electronic Ballast

Description

28 Watts

• CRI: 82+

Features

ALUMINUM **FLUORO BAR SYSTEM** T4 FLUORESCENT 2-WIRE

UNDERCABINET LIGHTING

ALFT4-28-4100



PROJECT

FIXTURE TYPE


MODEL

LAMP

CONTACT/TELEPHONE

Dimensions & Ordering Guide

MODEL NO. ALFT4-28-4100




Lumens

1540



Linkable with a link connector



Linkable

T4 Linkable Fluorescent Fixtures

Up to 8 units can be linked together, not to exceed 200W max.




LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736 E-mail: sales@liteline.com · Website: www.liteline.com With Ordering Guide, replace 4100K with 3200K where necessary. e.g. For 3200K, (ALFT4-6-3200)

Product specifications subject to change without notice.

Dimensions



Durable extruded aluminum fixture with shatter guard clear lens, in white

enamel body only. ALFT4-28-4100 comes with on/off switch on body. Complete with a 6 ft, power cord with plug, mounting hardware, link

connector, and a 4100K 28W fluorescent bulb.

Colour temperature: 4100K (Cool White) Lamps are rated for average 10,000 hrs

Can be hardwired (using ALFT6300)

Housing

Durable extruded aluminum fixture in white paint enamel body only.

Mounting

Hardware provided for mounting fixture either to standard horizontal surface or to vertical wall surface.

Ballast: Built-in Silent Electronic Ballast, AC120V -50-60 Hz

Dimmable: Not Dimmable

Input: 120V AC, 50-60Hz

Optional Accessories

A hardwire box - ALFT6300-WH

· Flexible wire connectors, available in various lengths -FBT6106 - 6" Connector Cable -FBT6100 - 12" Connector Cable -FBT6124 - 24" Connector Cable -FBT6136 - 36" Connector Cable





• Replacement lamp - T4-28W41

Listings