

Specifications

Lamp Wattage / Type

• Flicker free start up · Light weight

Seven available lengths · Polycarbonate clear lens reflector

T4 Replaceable Fluorescent lamp

Built-in Silent Electronic Ballast

Description

20 Watts

CRI: 82+

Features

Linkable

Housing

Mounting

.

.

•

.

# ALUMINUM **FLUORO BAR SYSTEM**

Durable extruded aluminum fixture with shatter guard clear lens, in white

enamel body only. ALFT4-20-4100 comes with on/off switch on body. Complete with a 6 ft. power cord with plug, mounting hardware, link

connector, and a 4100K 20W fluorescent bulb.

Colour temperature: 4100K (Cool White)

Lamps are rated for average 10,000 hrs

Efficient T4 Fluorescent Light Source

Can be hardwired (using ALFT6300)

Durable extruded aluminum fixture in white paint enamel body only.

Hardware provided for mounting fixture either to standard horizontal

Ballast: Built-in Silent Electronic Ballast, AC120V -50-60 Hz

**T4 FLUORESCENT 2-WIRE** UNDERCABINET LIGHTING

ALFT4-20-4100



PROJECT

FIXTURE TYPE

MODEL LAMP


CONTACT/TELEPHONE

# **Dimensions & Ordering Guide**


MODEL NO. ALFT4-20-4100

Lumens 1100


#### Dimensions







#### Linkable with a link connector



Linkable

#### **T4 Linkable Fluorescent Fixtures**

Up to 8 units can be linked together, not to exceed 200W max.



Listings

### LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736 E-mail: sales@liteline.com · Website: www.liteline.com With Ordering Guide, replace 4100K with 3200K where necessary. e.g. For 3200K, (ALFT4-6-3200) Product specifications subject to change without notice.

> ©Copyright 2007 Liteline Corporation. 09.04.08

## Dimmable: Not Dimmable

Input: 120V AC. 50-60Hz

#### **Optional Accessories**

· A hardwire box - ALFT6300-WH

surface or to vertical wall surface.

Flexible wire connectors, available in various lengths -FBT6106 - 6" Connector Cable -FBT6100 - 12" Connector Cable -FBT6124 - 24" Connector Cable -FBT6136 - 36" Connector Cable Replacement lamp - T4-20W41

