

50W MR16 GU10 Halogen Lamp Line Voltage Halogen Lamps

| PROJECT |
|-------------------|
| FIXTURE TYPE |
| MODEL |
| LAMP |
| CONTACT/TELEPHONE |

Product No.

LMP16GU10C-50-BX

Description

An MR16 line voltage multi-faceted reflector halogen lamp, with clear cover. For use in track fixtures.

General Characteristics

| Lamp Type | Line Voltage Halogen |
|------------|----------------------|
| Bulb Size | MR16 |
| Base | GU10 |
| Wattage | 50W |
| Voltage | 120V AC |
| Rated Life | 2,000 hours |
| Reflector | Dichroic |
| | |

Operating Characteristics

| Approx. Initial Lumens | 420 |
|-------------------------------|----------|
| Approx. Mean Lumens | 400 |
| Colour Temperature | 2750K |
| Colour Rendering Index. (CRI) | 99 |
| Beam Spread | 36° |
| Dimmable | Dimmable |

Dimensions

| Maximum Overall Length (MOL) | 2.13" (54.00mm) |
|------------------------------|-----------------|
| Bulb Diameter (DIA) | 2.00" (50.80mm) |

Applications:

- Retail store display
- Focus lighting



A Caution

- Lamp may shatter and cause injury if broken
 - Do not use excessive force when installing lamp.
 - Use only on dry location.




Warning


- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.

LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736 Email: sales@liteline.com • Website: liteline.com







Product specifications subject to change without notice.