



16W T4 Fluorescent Lamp

Fluorescent Lamps

PROJECT
FIXTURE TYPE
MODEL
LAMP
CONTACT/TELEPHONE


Product No. **T4-16W41**

Description

T4 Triphosphor fluorescent lamp, high colour rendering, 4100K colour temperature, long life, and rapid start.

General Characteristics

Lamp Type	Fluorescent Lamp
Bulb Size	T4
Base	Mini Bi-Pin
Wattage	16W
Voltage	NA
Frequency	60Hz
Current	220mA
Rated Life	10,000 hours
Minimum Operating Temperature	0°C
Reflector	NA
Ballast	Required
Transformer	Not Required



Operating Characteristics

Approx. Initial Lumens	880
Approx. Mean Lumens	640
Colour Temperature	4100K
Colour Rendering Index. (CRI)	82
Beam Spread	NA
Dimmable	Not dimmable

Dimensions

Maximum Overall Length (MOL)	18.82" (478.00mm)
Bulb Diameter (DIA)	0.53" (13.49mm)

Caution

- Lamp may shatter and cause injury if broken
 - Do not use excessive force when installing lamp.
 - Use only on dry location.

Warning

- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.



LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7
 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736
 Email: sales@liteline.com • Website: www.liteline.com

Product specifications subject to change without notice.