



# 20W T4 Fluorescent Lamp

## Fluorescent Lamps

PROJECT
FIXTURE TYPE
MODEL
LAMP
CONTACT/TELEPHONE

**Product No.** *T4-20W32*

### Description

T4 Triphosphor fluorescent lamp, high colour rendering, 3200K colour temperature, long life, and rapid start.

### General Characteristics

Lamp Type	<i>Fluorescent Lamp</i>
Bulb Size	<i>T4</i>
Base	<i>Mini Bi-Pin</i>
Wattage	<i>20W</i>
Voltage	<i>NA</i>
Frequency	<i>60Hz</i>
Current	<i>280mA</i>
Rated Life	<i>10,000 hours</i>
Minimum Operating Temperature	<i>0°C</i>
Reflector	<i>NA</i>
Ballast	<i>Required</i>
Transformer	<i>Not Required</i>



### Operating Characteristics

Approx. Initial Lumens	<i>1100</i>
Approx. Mean Lumens	<i>800</i>
Colour Temperature	<i>3200K</i>
Colour Rendering Index. (CRI)	<i>82</i>
Beam Spread	<i>NA</i>
Dimmable	<i>Not dimmable</i>

### Dimensions

Maximum Overall Length (MOL)	<i>20.59" (523.00mm)</i>
Bulb Diameter (DIA)	<i>0.53" (13.49mm)</i>

### ⚠ Caution

- Lamp may shatter and cause injury if broken
  - Do not use excessive force when installing lamp.
  - Use only on dry location.

### ⚠ Warning

- Risk of Electric Shock
  - Turn power off before inspection, installation or removal.



### LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7  
 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736  
 Email: sales@liteline.com • Website: www.liteline.com

**Product specifications subject to change without notice.**