



8W T4 Fluorescent Lamp

Fluorescent Lamps

PROJECT
FIXTURE TYPE
MODEL
LAMP
CONTACT/TELEPHONE


Product No. *T4-8W41*

Description

T4 Triphosphor fluorescent lamp, high colour rendering, 4100K colour temperature, long life, and rapid start.

General Characteristics

Lamp Type	<i>Fluorescent Lamp</i>
Bulb Size	<i>T4</i>
Base	<i>Mini Bi-Pin</i>
Wattage	<i>8W</i>
Voltage	<i>NA</i>
Frequency	<i>60Hz</i>
Current	<i>110mA</i>
Rated Life	<i>10,000 hours</i>
Minimum Operating Temperature	<i>0°C</i>
Reflector	<i>NA</i>
Ballast	<i>Required</i>
Transformer	<i>Not Required</i>



Operating Characteristics

Approx. Initial Lumens	<i>440</i>
Approx. Mean Lumens	<i>320</i>
Colour Temperature	<i>4100K</i>
Colour Rendering Index. (CRI)	<i>82</i>
Beam Spread	<i>NA</i>
Dimmable	<i>Not dimmable</i>

Dimensions

Maximum Overall Length (MOL)	<i>13.07" (332.00mm)</i>
Bulb Diameter (DIA)	<i>0.53" (13.49mm)</i>

Caution

- Lamp may shatter and cause injury if broken
 - Do not use excessive force when installing lamp.
 - Use only on dry location.

Warning

- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.



LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7
 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736
 Email: sales@liteline.com • Website: www.liteline.com

Product specifications subject to change without notice.