



# 24W T4 Fluorescent Lamp

## Fluorescent Lamps

PROJECT
FIXTURE TYPE
MODEL
LAMP
CONTACT/TELEPHONE

Product No. **T4-24W41**

### Description

T4 Triphosphor fluorescent lamp, high colour rendering, 4100K colour temperature, long life, and rapid start.

### General Characteristics

Lamp Type	Fluorescent Lamp
Bulb Size	T4
Base	Mini Bi-Pin
Wattage	24W
Voltage	NA
Frequency	60Hz
Current	330mA
Rated Life	10,000 hours
Minimum Operating Temperature	0°C
Reflector	NA
Ballast	Required
Transformer	Not Required



### Operating Characteristics

Approx. Initial Lumens	1320
Approx. Mean Lumens	960
Colour Temperature	4100K
Colour Rendering Index. (CRI)	82
Beam Spread	NA
Dimmable	Not dimmable

### Dimensions

Maximum Overall Length (MOL)	33.98" (863.00mm)
Bulb Diameter (DIA)	0.53" (13.49mm)

### Caution

- Lamp may shatter and cause injury if broken
  - Do not use excessive force when installing lamp.
  - Use only on dry location.

### Warning

- Risk of Electric Shock
  - Turn power off before inspection, installation or removal.



### LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7  
 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736  
 Email: sales@liteline.com • Website: www.liteline.com

**Product specifications subject to change without notice.**