

TRACK LIGHTING TRACKS AND **ACCESSORIES** 12 FOOT TRACK



Model

TK6012-BK

PROJECT

FIXTURE TYPE

MODEL

LAMP

CONTACT/TELEPHONE

Specifications

Description

Extruded 12 ft. aluminum track with 20-amp rated flat, solid integral conductors. These tracks can be joined together using any of the track connectors.

Available in three colours: Black, White and Brushed Nickel.

Features

- Extruded aluminum construction
- · Low profile aesthetic design
- Solid 12-gauge conductors
- Polarity groove
- Surface or stem mounted (mounting hardware supplied)

Extrusion

0.030" die cast aluminum construction with 0.045" PVC insulators holding 12 gauge flat conductor wiring. Polarity groove is located on face of track to indicate location of grounding conductor.

Electrical

System Electrical Rating: 20A, 120V, 60Hz Note: Track lighting is a single circuit electrical distribution system designed to supply power to lighting units in flexible ways.

Compatibility

Liteline Track system is compatible with all Liteline Track accessories and connectors.

1-Circuit Track

Single circuit track is available for 120V applications. Single hot and neutral conductors are rated for 20 Amps per branch circuit. Copper electrical conductors are concealed in an insulating thermo plastic low profile track cross-section.

TK6012-BN

Dimensions & Ordering Guide

White TK6012-WH **Brushed Nickel** 0

144" 3657mm


Colour

Black

1 3/8" / 35 mm

1 3/8" / 35 mm

All dimensions are in inches/ millimeters



Listings



LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736 E-mail: sales@liteline.com • Website: www.liteline.com Product specifications subject to change without notice.