



Analog Output Modules

Genius Analog Output blocks provide 6 channels of current and voltage outputs with powerful diagnostics.

	IC660BBA025	IC660BBA105
Product Name	Genius Analog Output Block, Current-source, 6 Channels, 24/48 VDC Powered	Genius Analog Output Block, Current-source, 6 Channels, 115 VAC/125 VDC Powered
Lifecycle Status	Mature	Mature
Network Support	Genius Bus	Genius Bus
Output Range	4 mA to 20 mA 0 mA to 24 mA	4 mA to 20 mA 0 mA to 24 mA
Number of Points	6 Outputs	6 Outputs
Points Per Common	One group of 6	One group of 6
Operating Voltage	18-56 VDC	93-132 VAC / 105-145 VDC
Resolution	6 micro Amp	6 micro Amp
Update Rate	25mS	25mS
Accuracy	0.15% of full-scale reading	0.15% of full-scale reading
Dimensions (W x H x D)	8.83" (22.44cm) x 3.50" (8.89cm) x 3.94" (10.00cm)	8.83" (22.44cm) x 3.50" (8.89cm) x 3.94" (10.00cm)