

Accessories

IC694TBB032	High Density 32 Point Terminal Block Box Style	Active
IC694TBB132	High Density 32 Point Terminal Block Box Style with Extended Shroud for Large Wiring Bundles	Active
IC694TBS032	High Density 32 Point Terminal Block Spring Style	Active
IC694TBS132	High Density 32 Point Terminal Block Spring Style with Extended Shroud for Large Wiring Bundles	Active
IC694TBC032	High Density 32 Point Terminal Block with a 40 pin Fujitsu connector. Compatible with DC Inputs, Analog Modules only. Not compatible with DC or AC output modules.	Target April 2012
IC694ACC310	Filler Module, Blank Slot	Active
IC694ACC311	Terminal blocks, 20 terminals (qty 6) for IC694xxx low density modules	Active
IC695ACC600	RX3i Cold Junction Compensation Kit (Contains 2 CJs) for Universal Analog and Thermocouple Input Modules	Active
IC698ACC701	Lithium Batter pack that installs in CPU for CPU310 and CMU310 only (28 days of continuous battery backup)	Active
IC693ACC302	External High capacity battery pack. (1.3 years of continuous battery backup for CPU310/CMU310 and 1 month for CPU320/CRU320.)	Active
IC690RBT001	Rechargeable battery kit. Includes battery (IC690RBT001) and battery charger (IC690CRG001). The rechargeable battery is compatible with PAC controllers CPU310,CPU315, CPU320 and CRU320 only. Also compatible with Series 90-30 and Series 90-70 CPUs.	Active
IC690CRG001	Battery charger. Compatible with rechargeable battery (IC690RBT001) only. The rechargeable battery is compatible with PAC controllers CPU310,CPU315, CPU320 and CRU320 only. Also compatible with Series 90-30 and Series 90-70 CPUs.	Active
IC690RBT001	Rechargeable battery is compatible with IC690CRG001 battery charger only. The rechargeable battery is compatible with PAC controllers CPU310, CPU315, CPU320 and CRU320 only. Also compatible with Series 90-30 and Series 90-70 CPUs., Series 90-30 and Series 90-70.	Active
IC690ACC001	Real Time Clock Battery for CPE305 and CPE310	Active
IC695ACC400	CPE305 and CPE310 CPU Battery-less Energy Pack for backing up dynamic data	Active
IC695CBL001	Energy Pack Cable	Active
IC690ACC901	Mini-Converter Kit with cable (RS-485/RS-232)	Active
IC690ACC903	RS-485 Port Isolator	Active
IC693CBL316	RS-232 cable for RX3i CPE305 programming port and also the Station Manager Cable for the Ethernet ETM001	Active
IC690CDR002	User Manuals, InfoLink CD-ROM Documentation, single-user license	Active
IC693ACC307	I/O Bus Terminator Plug	Active
IC693ACC311	Series 90-30 style IC693 I/O modules Terminal Blocks, 20 terminals (qty 6)	Active

External Power Supplies

IC690PWR024	24 VDC, 5 Amp Output Power and 120/230 VAC Input Power Power Supply	Active
IC690PWR124	24 VDC, 10 Amp Output Power and 120/230 VAC Input Power Power Supply	Active

Terminal Block Quick Connect

Terminal Block Quick Connect (TBQC) for selected I/O modules enables the user to easily connect interposing terminal blocks. The TBQC consists of an I/O faceplate adapter that includes a 24 pin Fujitsu male connector (the faceplate replaces the 20 screw terminal connector on front of I/O module, not compatible with the high density 36 screw terminals), cable and interposing terminal block.

TBQC I/O Module Face Plate Adapter

IC693ACC334	I/O module face plate adapter for 20 screw type I/O modules. Faceplate provides a 24 pin male Fujitsu connector.	Active
-------------	--	--------

TBQC Interposing Terminal Block

IC693ACC329	Interposing terminal block base for IC694MDL645, IC694MDL646, and IC694MDL240. The base can also be used with any 20 point terminal discrete or analog modules not listed.	Active
IC693ACC330	Interposing terminal block base for IC694MDL740 and IC694MDL742	Discontinued
IC693ACC331	Interposing terminal block base for IC694MDL741	Discontinued
IC693ACC332	Interposing terminal block base for IC694MDL940	Active
IC693ACC333	Interposing terminal block base for IC694MDL340	Active
IC693ACC337	Interposing terminal block base for IC693MDL654/655/752/753 and IC694MDL654/655/752/753	Active

TBQC Cables

IC693CBL327	Cable, Left Side, One -24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules.	Active
IC693CBL328	Cable, Right Side, One -24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules.	Active
IC693CBL329	Cable, Left Side, One -24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL330	Cable, Right Side, One -24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL331	Cable, Left Side, One -24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL332	Cable, Right Side, One -24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL333	Cable, Left Side, One -24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL334	Cable, Right Side, One -24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active

High Density Terminal Block Quick Connect (32 point I/O terminals)

High Density Terminal Block Quick Connect (TBQC) for selected I/O modules enables the user to easily connect interposing terminal blocks. The HDTBQC consist of a I/O module terminal block with a 40 pin Fujitsu male connector, cable and interposing terminal block. The HDTBQC is compatible with modules that accept IC694TBC032 (24 VDC discrete inputs and analog input and output modules. The HDTBQC is not compatible with discrete output modules).

HDTBQC I/O Module Face Plate Adapter

IC694TBC032	High Density 32 Point Terminal Block with a 40 pin Fujitsu connector. Compatible with DC Inputs, Analog Modules only. Not compatible with DC or AC output modules.	Active
-------------	--	--------

HDTBQC Interposing Terminal Block

IC694RTB032	Remote Terminal Block 36 Pin DIN-Rail mount	Target April 2012
HDTBQC Remote Terminal Base		
IC694CBL005	.5 meter Cable between IC694TBC032 and IC694RTB032	Target April 2012
HDTBQC Cables		
IC694CBL010	1.0 meter Cable between IC694TBC032 and IC694RTB032	Target April 2012
IC694CBL030	3.0 meter Cable between IC694TBC032 and IC694RTB032	Target April 2013
IC694CBL130	3 meter Cable with IC694TBC032 connector on one end and open wire on other end	Target April 2014

RMX and CMX Reflective Memory Fiber Optic Cables

Simplex LC to LC connector, Fiber-Optic Cable – Multimode 62.5 Micron core.

Simplex (single) cabling is used for daisy chaining Tx to Rx to/from another node until final device circles back to beginning node.

Each CMX module requires two Simplex cables per module.

CBL-000-F5-000	.5 feet (0.15 m)	Active
CBL-000-F5-001	1 foot (.31 m)	Active
CBL-000-F5-002	5 feet (1.52 m)	Active
CBL-000-F5-003	10 feet (3.04 m)	Active
CBL-000-F5-004	25 feet (7.62 m)	Active
CBL-000-F5-005	50 feet (15.24 m)	Active
CBL-000-F5-006	80 feet (24.40 m)	Active
CBL-000-F5-007	100 feet (30.49 m)	Active
CBL-000-F5-008	150 feet (45.72 m)	Active
CBL-000-F5-009	200 feet (60.98 m)	Active
CBL-000-F5-010	250 feet (76.20 m)	Active
CBL-000-F5-011	350 feet (106.68 m)	Active
CBL-000-F5-012	500 feet (152.15 m)	Active
CBL-000-F5-014	656 feet (200 m)	Active
CBL-000-F5-015	820 feet (250 m)	Active
CBL-000-F5-016	1,000 feet (304.30 m)	Active

Duplex LC to LC connector, Fiber-Optic Cable - Multimode 62.5 Micron core.

Duplex cabling is generally used with RMX system and is also good for CMX module to HUB connections. Duplex has a pair of cables connected together.

Each CMX module requires one Duplex cable per module to a hub.

CBL-000-F6-000	3 feet (0.9144 m)	Active
CBL-000-F6-001	6 feet (1.8288 m)	Active
CBL-000-F6-002	10 feet (3.048 m)	Active
CBL-000-F6-003	16 feet (4.8768 m)	Active
CBL-000-F6-004	32 feet (9.7536 m)	Active
CBL-000-F6-005	66 feet (20.1168 m)	Active
CBL-000-F6-006	98 feet (29.8704 m)	Active
CBL-000-F6-007	164 feet (49.9872 m)	Active
CBL-000-F6-008	230 feet (70.104 m)	Active
CBL-000-F6-009	328 feet (99.9744 m)	Active
CBL-000-F6-010	393 feet (119.7864 m)	Active
CBL-000-F6-011	426 feet (129.8448 m)	Active
CBL-000-F6-012	492 feet (149.9616 m)	Active
CBL-000-F6-013	557 feet (169.7736 m)	Active
CBL-000-F6-014	656 feet (199.9488 m)	Active
CBL-000-F6-015	721 feet (219.7608 m)	Active
CBL-000-F6-016	754 feet (229.8192 m)	Active
CBL-000-F6-017	820 feet (249.936 m)	Active
CBL-000-F6-018	885 feet (269.748 m)	Active
CBL-000-F6-019	984 feet (299.9232 m)	Active

Reflective Memory Interface Modules for PCs

PMC 5565 Reflective Memory PMC Module

PMC-5565PIORC-110000	PMC, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PMC-5565PIORC-111000	PMC, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4 K FIFOs, Single Mode Transmission	Active
PMC-5565PIORC-210000	PMC, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PMC-5565PIORC-211000	PMC, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4 K FIFOs, Single Mode Transmission	Active

PCI 5565 Reflective Memory PCI Module

PCI-5565PIORC-110000	PCI, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCI-5565PIORC-111000	PCI, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active
PCI-5565PIORC-210000	PCI, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCI-5565PIORC-211000	PCI, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active

PCI Express 5565 Reflective Memory PCIE Module

PCIE-5565RC-100000	PCI Express, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCIE-5565RC-101000	PCI Express, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active
PCIE-5565RC-200000	PCI Express, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCIE-5565RC-201000	PCI Express, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active

CMX and RMX Reflective Memory HUB (Contact GE for additional HUB configurations)

HUB-5595-308	DIN-Rail Mount Reflective Memory Hub. 21 -32 VDC Power supply, 1x 10BaseT Ethernet, 1x RS232, 8x Multimode Pluggable transceivers	Active
HUB-5595-380	DIN-Rail Mount Reflective Memory Hub. 21 -32 VDC Power supply, 1x 10BaseT Ethernet, 1x RS232, 8x Single mode Pluggable transceivers	Active
ACC-5595-208	Rack Mount or Desktop Reflective Memory Hub. Universal power supply, 1x 10BaseT Ethernet, 1x RS232, 8x multimode pluggable transceivers	Active
ACC-5595-280	Rack Mount or Desktop, 8 Single mode Pluggable Transceivers. And no Multimode Pluggable Transceivers	Active

Starter Kits (Only one starter kit per customer per customer site)

IC695STK001	RX3i Controller PACKage 1 Starter Kit includes RX3i with software. (includes one each IC695CPU305, IC695CHS012, IC695LRE001, IC695PSA040, IC695ETM001, IC694ACC300, IC694MDL940 and IC646MPP001.) Limited one RX3i starter kit per customer site.	Active
IC695STK002	RX3i with Control and View. Power PACKage 2 Starter Kit includes RX3i and QuickPanel View 6" STD with software. (includes one each IC695CPU305, IC695CHS012, IC695LRE001, IC695PSA040, IC695ETM001, IC694ACC300, IC694MDL940, IC754VSI06STD, BC646MQP001, IC646MPP001 and DC power supply for QuickPanel) Limited one RX3i starter kit per customer site.	Active
IC695STK003	RX3i, The Complete PACKage with Control, Motion and View. Power PACKage 3 Starter Kit includes RX3i, motion module (Servo and Amplifier sold separately) and QuickPanel View 6" STD with software. (includes one each IC695CPU305, IC695CHS012, IC695LRE001, IC695PSA040, IC695ETM001, IC694DSM314, IC694ACC300, IC694MDL940, IC754VSI06STD, BC646MQP001, IC646MPP001 and DC power supply for QuickPanel) Limited one RX3i starter kit per customer site.	Active
IC695STK004	RX3i Power PACKage 4 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSA040, IC695ETM001, IC646MPP101)	Active
IC695STK005	RX3i Power PACKage 5 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSA040, IC646MPP101)	Active
IC695STK006	RX3i Power PACKage 6 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSD040, IC695ETM001, IC646MPP101)	Active
IC695STK007	RX3i Power PACKage 7 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSD040, IC646MPP101)	Active
IC695STK010	RX3i Profinet Power PACKage 10. Kit includes CPE305, 7 slot base, AC power supply, input and output module, Profinet controller, VersaMax Profinet slave, combination I/O and Proficy Machine Edition. (one each IC695CPU305, IC695CHS007, IC695PSA040, IC694ACC300, IC694MDL740, IC200PNS001, IC200PWR102, IC200MDD844, IC200ACC302, IC200CHS002, IC646MPP101)	Active