

Baseplates

Series 90-30 baseplates are available in 5- and 10-slot configurations to meet the needs of your application. You can choose expansion or remote baseplates for multi-rack systems, covering distances of up to 700 feet from the CPU. GE offers standard length cables for easy installation and provides wiring information for custom applications.



	IC693CHS391	IC693CHS392	IC693CHS393	IC693CHS397	IC693CHS398	IC693CHS399
Product Name	10-slot CPU Baseplate (Model 331 and above)	10-slot Expansion Baseplate (Model 331 and above)	10-slot Remote Baseplate (Model 331 and above)	5-slot CPU Baseplate (Model 331 and above)	5-slot Expansion Baseplate (Model 331 and above)	5-slot Remote Baseplate (Model 331 and above)
Module Type	CPU I/O Base	Expansion I/O Base	Expansion I/O Base	CPU I/O Base	Expansion I/O Base	Expansion I/O Base
Baseplate Option	Main (With CPU Slot)	Expansion	Expansion	Main (With CPU Slot)	Expansion	Expansion
Distance	N/A	Up to 50 feet	Up to 700 feet	N/A	Up to 50 feet	Up to 700 feet
Number of Slots	10	10	10	5	5	5
Dimension (WxHxD) in. (mm)	17.44x5.12x5.59 (443x130x142)	17.44x5.12x5.59 (443x130x142)	17.44x5.12x5.59 (443x130x142)	10.43x5.12x5.59 (245x130x142)	10.43x5.12x5.59 (245x130x142)	10.43x5.12x5.59 (245x130x142)
Internal Power Used	420 mA @ 5 VDC	150 mA @ 5 VDC	460 mA @ 5 VDC	270 mA @ 5 VDC	170 mA @ 5 VDC	480 mA @ 5 VDC