



Specs for Category C6 Unshielded Patch Cord

Part no. PC-LPM-UTP-RJ45-C6-YY-XX

Construction characteristic features



Materials

Cable

Conductor: 7 copper wires Ø0.20 mm (0.008"), 24 AWG

Insulation: High Density Polyethylene (HDPE)

Diameter of insulated conductor: 0.98 ± 0.05 mm (0.039" ± 0.002")

Number of pairs: 4

Color of twisted pairs: blue-white/blue, orange-white/orange, green-white/green, brown-white/brown

Plugs

2 pieces RJ-45 8P8C, category 6, for patch cable

Contact: 1.27 micron (50 microinches) gold plated copper alloy

Latch guard Material: PVC

Ordering

Available in:

XX = White, Black, Blue, Green, Grey, Orange, Red, Violet, Yellow



Toll Free: +1-866-634-9737



Toll Free: +1-888-497-3748

www.hyperline.com | info@hyperline.com

2212 Gladwin Crescent, Unit C7, Ottawa, Ontario, K1B 5N1, Canada

Available in:

YY = 1F, 2F, 3F, 4F, 5F, 7F, 10F, 15F, 25F



Toll Free: +1-866-634-9737



Toll Free: +1-888-497-3748

www.hyperline.com | info@hyperline.com

2212 Gladwin Crescent, Unit C7, Ottawa, Ontario, K1B 5N1, Canada