

Specs for HDMI Cable A Male to A Male type

Part no. PC-HDMI-12B1-YY-BK



Description:

Male to male, 24k gold plated, 1.4v, full 1080 30AWG, 5P+4C

HDMI cable is a high-quality cable featuring multi-stranded copper conductors for highest possible signal strength and maximum frequency response.

Featured are corrosion-resistant gold connectors ensuring high conductivity for the best possible picture while supporting the highest resolution standards.

Specifications

19 Pin Gold-plated connectors for highest signal transfer rate and resistance in corrosion.
Fully HDCP compliant to provide highest level of signal quality.
Fully compliant to V1.4 specification.
Supports Transfer Digital Audio and Video signals at warp speed of 10.2 Gigabits per second
Full support 480i, 480p, 720p, 1080i, 1080p, 1044P resolution
HDMI Ethernet Channel, Audio Return Channel
3D Support, 4K x 2K Support

Mechanical characteristics

Center Conductor Size: 30AWG, 26AWG
Center Conductor Material: Bare Copper
Insulation: Foam PE and Polypropylene
Shielding Material: Aluminum Mylar
Shielding Coverage: 100% Coverage plus 25% Overlap
Connector Contact Plating: Gold Plated, 10Micro Inches Minimum
Drain Wires: 30AWG Bare Copper
Braiding: Aluminum
Braiding Coverage: 70% Minimum
Outside Material: Conductor Gauge Dependent
Compliance: HDMI and ROHS



Toll Free: +1-866-634-9737



Toll Free: +1-888-497-3748

www.hyperline.com | info@hyperline.com

2212 Gladwin Crescent, Unit C7, Ottawa, Ontario, K1B 5N1, Canada

Ordering

Available in:

YY = 3F, 6F, 10F, 15F, 25F, 50F



Toll Free: +1-866-634-9737



Toll Free: +1-888-497-3748

www.hyperline.com | info@hyperline.com

2212 Gladwin Crescent, Unit C7, Ottawa, Ontario, K1B 5N1, Canada