



Search Search Options

visit our other sites: [FTZ](#) | [Utilco](#) | [IlSCO Canada](#)

[My IlSCO](#) | [Home](#) | [About Us](#) | [Products](#) | [Reference](#) | [Customer Service](#) | [Contact Us](#) | [Distributors](#) | [Price & Availability](#)

CRA 1 HOLE, SHORT BARREL

- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Sight hole and chamfered barrel for visual inspection of proper cable insertion.
- Color Coded.
- Maximum conductivity and excellent crimping characteristics.
- Range-taking with ILSCO dieless tools and Burndy Y644M dieless tool.
- UL 486A 90°C Listed and CSA Certified for 600 Volts.
- If proper high voltage spacings and insulation techniques are used, may be used for high voltage applications up to 35KV.
- For Copper Conductor only.
- Please see IlSCO's BT(Blank Tang) Line for other bolt size options.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools. Refer to Tool and Die Charts under Reference Tab.
- UL File E6207



Narrow Criteria by Wire Size by Bolt/Stud Size

* Catalog Numbers link to CAD files (if available)

Catalog No.	Wire Size	Expanded Wire Size	Welding Cable Size	Bolt Size	Color Code	Die Index	Tang Width	N.A.E.D. No.
CRA-8	8 STR.	-	-	#10	RED	1	13/32	78366905449
CRA-6	6 STR.	-	8 WELD	#10	BLUE	2	13/32	78366905342
CRB-6	6 STR.	-	8 WELD	1/4	BLUE	2	13/32	78366908850
CRA-4	4 STR.	4-6 STR.	6 WELD	#10	GREY	3	1/2	78366904238
CRA-4-516	4 STR.	4-6 STR.	6 WELD	5/16	GREY	3	1/2	78366905239
CRB-4	4 STR.	4-6 STR.	6 WELD	1/4	GREY	3	1/2	78366908746
CRA-3	3 STR.	3-6 STR.	-	1/4	WHITE	3	17/32	78366905110
CRA-2	2 STR.	2-6 STR.	4 WELD	1/4	BROWN	4	19/32	78366905115
CRB-2	2 STR.	2-6 STR.	4 WELD	5/16	BROWN	4	19/32	78366908623
CRC-2	2 STR.	2-6 STR.	4 WELD	3/8	BROWN	4	19/32	78366908625
CRA-1	1 STR.	1-6 STR.	2 WELD	5/16	GREEN	4	11/16	78366905051
CRA-1-14	1 STR.	1-6 STR.	2 WELD	1/4	GREEN	4	11/16	78366905052
CRA-1-38	1 STR.	1-6 STR.	2 WELD	3/8	GREEN	4	11/16	78366905053
CRA-0	1/0 STR.	1/0-6 STR.	1 WELD	5/16	PINK	5	3/4	78366905000
CRB-0	1/0 STR.	1/0-6 STR.	1 WELD	3/8	PINK	5	3/4	78366908519
CRA-0-14	1/0 STR.	1/0-6 STR.	1 WELD	1/4	PINK	5	3/4	78366905005
CRA-2/0	2/0 STR.	2/0-4 STR.	1/0 WELD	3/8	BLACK	6	3/4	78366905676
CRA-2/0-14	2/0 STR.	2/0-4 STR.	1/0 WELD	1/4	BLACK	6	13/16	78366905680
CRB-2/0	2/0 STR.	2/0-4 STR.	1/0 WELD	5/16	BLACK	6	13/16	78366908900
CRA-3/0	3/0 STR.	3/0-2 STR.	2/0 WELD	3/8	ORANGE	9	29/32	78366905721
CRA-3/0-14	3/0 STR.	3/0-2 STR.	2/0 WELD	1/4	ORANGE	9	29/32	78366905725
CRB-3/0	3/0 STR.	3/0-2 STR.	2/0 WELD	1/2	ORANGE	9	29/32	78366909503

CRC-3/0	3/0 STR.	3/0-2 STR.	2/0 WELD	5/16	ORANGE	9	29/32	78366909506
CRA-4/0	4/0 STR.	4/0-1 STR.	3/0 WELD	3/8	PURPLE	10	1	78366905780
CRA-4/0-14	4/0 STR.	4/0-1 STR.	3/0 WELD	1/4	PURPLE	10	1	78366905782
CRB-4/0	4/0 STR.	4/0-1 STR.	3/0 WELD	1/2	PURPLE	10	1	78366909626
CRC-4/0	4/0 STR.	4/0-1 STR.	3/0 WELD	5/16	PURPLE	10	1-3/32	78366909628
CRA-250	250 MCM	250 MCM-1/0 STR.	4/0 WELD	1/2	YELLOW	11	1-3/32	78366906433
CRA-250-38	250 MCM	250 MCM-1/0 STR.	4/0 WELD	3/8	YELLOW	11	1-3/32	78366906434
CRA-300	300 MCM	300 MCM-2/0 STR.	-	1/2	WHITE	12	1-3/16	78366906556
CRA-300-38	300 MCM	300 MCM-2/0 STR.	-	3/8	WHITE	12	1-3/16	78366906557
CRA-300-58	300 MCM	300 MCM-2/0 STR.	-	5/8	WHITE	12	1-3/16	78366906559
CRA-300-516	300 MCM	300 MCM-2/0 STR.	-	5/16	WHITE	12	1-3/16	78366906558
CRA-350	350 MCM	350 MCM-3/0 STR.	-	1/2	RED	13	1-9/32	78366905844
CRA-400	400 MCM	400 MCM-4/0 STR.	-	5/8	BLUE	14	1-3/8	78366906767
CRA-400-12	400MCM	400 MCM-4/0 STR.	-	1/2	BLUE	14	1-3/8	78366906768
CRA-500	500 MCM	500 MCM-250 MCM	-	5/8	BROWN	15	1-17/32	78366906863
CRA-500-12	500 MCM	500 MCM-250 MCM	-	1/2	BROWN	15	1-17/32	78366906865
CRA-600	600 MCM	600 MCM-350 MCM	-	5/8	GREEN	16	1-11/16	78366907040
CRA-600-12	600MCM	600 MCM-350 MCM	-	1/2	GREEN	16	1-11/16	78366907041
CRA-700	700 MCM	700 MCM-350 MCM	-	5/8	PINK	16A	1-25/32	78366907080
CRA-750	750 MCM	750 MCM-500 MCM	-	5/8	BLACK	17	1-29/32	78366907081
CRA-1000	1000 MCM	1000 MCM-750 MCM	-	5/8	WHITE	18	2-3/16	78366907436

