



OEM POPULAR ITEMS



Isolateur # R-16



PDC... PDA...



TA...-I



SLU...



AU...-I



N8020A04T0



N8020A04T



N8020A108T



N8020-UNAS



NB-120-AS



N-174-AS & N-174-UNAS = CU tube

N8237 = Brass Bar



D-167...

Model Number	Type of wire	Nr. of Holes	Nr. of Screws included	Type of Screws included	Wire Range		Dimensions			Bolt Hole Size	Number of mounting holes	Mounting Hole Position		
					Main Wire	Tap Wire	Long mm	H Height with maximum wire mm	Wide mm			Distance in mm from end of Bar to First Mounting	Distance in mm between holes center	
N8020A04T0	CU-AL	4	3	E-199	none	4-14	33	16	8	#10	1	12,5		
N8020A04T	CU-AL	4	3	E-8197	none	4-14	33	19	8	#10	1	12,5		
N8020A108T	CU-AL	10	8	E-8197	none	4-14	80	19	8	#10	2	12,5	56,0	
N8020-UNAS	CU-AL	231	0	none	none	4-14	1829		8		0			
NB-120-AS	CU-AL	120	120	2 types	30 x 1/0-14	90 x 6-14	990		9		0			
D167-4	CU	6	4	E-153	4-14	6-14	70	19	9	#10	2	14,7	50,3	
D167-6	CU	8	6	E-153	4-14	6-14	89	19	9	#10	2	24,8	50,3	
D167-8	CU	10	8	E-153	4-14	6-14	113	19	9	#10	2	34,9	50,3	
D167-10	CU	12	10	E-153	4-14	6-14	130	19	9	#10	2	45,0	50,3	
D167-12	CU	14	12	E-153	4-14	6-14	151	19	9	#10	2	55,1	50,3	
D167-14	CU	16	14	E-153	4-14	6-14	171	19	9	#10	2	65,2	50,3	
N8237A01T	CU	7	5	E-153	none	4-14	57	16	8	#10	2	4,0	47,5	
N8237A00T	CU	17	15	E-153	none	4-14	136	16	8	#10	2	45,0	47,5	
N-174-AS	CU	174	174	E-153	none	6-14	1753	19	9		0			
N-174-UNAS	CU	174	0	none	none	6-14	1753	19	9		0			
E0199C00C3	Screws 1/4 x 28 - Flat Head for Flat screwdriver						9							
E-153	Screws 1/4 x 28 - Flat Head for Flat screwdriver						11							
E8197C00Z	Screws 1/4 x 28 - Round head for Square & Flat scrdvr						13							