

## LONG LENGTH COPPER NEUTRAL BAR





**TYPE** N174

### **Features**

- Manufactured from high strength copper tubingRange taking
- UL Recognized and CSA certified for 600 volts

### Benefits

- Provides maximum conductivity
   A wide range of conductor sizes can be used in the same connector
- Ensures reliability for copper conductor



	Number Of Taps	Wire Range						
Catalog Number			L	W	Н	Height With Maximum Wire	Mounting Holes	Distance Between Holes
N-174 Unassem. *	174	6-14	69.0	.343	.468	.75	None	.397"
N-174 Assembled **	174	6-14	69.0	.343	.468	.75	None	.397"

<sup>\*</sup> Please order screws separately Part Number E153 (Screws)

Note: E153 screws use flathead screwdriver UL Recognizedas D167

## LONG LENGTH ALUMINUM NEUTRAL BAR






# **TYPE** N8020

- Manufactured from high strength aluminum alloy
- Range taking
- UL Recognized and CSA certified for 600 volts
- Electro-tin plated

- Suitable for either copper or aluminum conductors
  A wide range of conductor sizes can be used in the
- same connector
   Ensures reliability
- Provides low contact resistance



Catalog Number	Number Of Taps	Wire Range	Dimensions						Mounting Hole Positions	
			L	W	Н	Height With Maximum Wire	Bolt Size	Mounting Holes	From End Of Bar To First Mounting Hole	Distance Between Holes
N8020A00T	231	4-14	72.0	.312	.437	.75	N/A	None	N/A	.312"
N8020 Unassembled *	231	4-14	72.0	.312	.437	.75	N/A	None	N/A	.312"
N8020A108T	10	4-14	3.168	.312	.437	.75	#10	.203 (#2,#9 holes)	.492	.312"
N8020A104T	4	4-14	1.296	.312	.437	.75	1/4 - 28	None	N/A	.312"

<sup>\*</sup> Please order screws separately Part Numer E199 (Screws) Note: E199 screws use flathead screwdriver



<sup>\*\*</sup> Assembled complete with E153 screws