

On-Q/Legrand® Home Systems evōQ™ 1000 Series Speakers

evōQ™ 1000 Series Speakers bring whole-house audio distribution to a price point that any buyer can afford — without sacrificing quality sound. In fact, these speakers rank among the highest in value in their price range on today's market. Sold in pairs, the high-efficiency speakers install in a snap by utilizing self-centering screw heads and can be used with On-Q Pre-Construction Brackets.



evōQ™ 1000 SERIES, 6.5" IN-WALL AND IN-CEILING SPEAKER


Feature poly fiber woofers, PEI mylar tweeters and foam gaskets to minimize vibration and provide air-tight seal.

Frequency response is 60 Hz to 20 KHz. RMS power is 50 W, with peak power handling reaching 100 W.

- Attractive white finish with grill, included, can be painted to match any décor.



364765-02
In-Wall



364764-02
In-Ceiling

Suitable for moisture rich environments.


evōQ™ 1000 SERIES SPEAKERS

PART #	DESCRIPTION	FREQUENCY	EFFICIENCY	POWER RMS / PEAK	IMPEDANCE	TWEETER	WOOFER
364765-02	6.5" In-Wall Speaker (pair)	60 Hz to 20 Hz	90 dB	50 W / 100 W	8 Ohms	0.75" Mylar	6.5" Poly
364764-02	6.5" In-Ceiling Speaker (pair)	60 Hz to 20 Hz	90 dB	50 W / 100 W	8 Ohms	0.75" Mylar	6.5" Poly

IMPEDANCE AUDIO DISTRIBUTION

Provides color-coded connections for up to six sets of speakers with impedance.

Features removable connectors for easy wire termination.



364454-01



364769-01

- 75 W RMS volume control runs impedance matching through jumpers on the back.
- Allows sets of speakers (2x 4x 8x) to be added without loss of volume control.

ON-Q AUDIO DISTRIBUTION

PART #	DESCRIPTION	PART #	DESCRIPTION
364454-01	6 Room Audio Module	364769-01 (White)	Speaker/Impedance Matching Volume Control
364741-01 (White)	4-Zone Audio Distribution Outlet	364769-02 (Almond)	Speaker/Impedance Matching Volume Control
364741-02 (Almond)	4-Zone Audio Distribution Outlet	364769-03 (Ivory)	Speaker/Impedance Matching Volume Control
364741-03 (Ivory)	4-Zone Audio Distribution Outlet	364520-01 (White)	Impedance Matching Volume Control
		364520-03 (Ivory)	Impedance Matching Volume Control