

## lyriQ™ AUDIO MODULE AND INPUTS

Converts line level audio and control (RCA connection) to Cat 5.

Three IR-emitter outputs and one IR target input allows for control of multi-media equipment stored in an entertainment center.



F7398

### FEATURES

- Gold-plated RCA Jacks help ensure optimum audio performance.
- 38 KHz filter can be applied to emitter output 3 for devices that are sensitive to that frequency band.



Dedicated source selection up to four zones when used with multi-source system. Fixed to source 1 when used with single source system.

Adjustable backlight levels for increasing or decreasing illumination.

Infrared sensors allow easy remote control of volume level and whole house commands.

Built-in amplifier powers speakers.

## RELATED PRODUCTS



LOCAL SOURCE INPUT  
F7417-WH (WHITE)



AMPLIFIED KNOB  
VOLUME CONTROL  
WITH IR  
F7399-WH (WHITE)



DUAL IR MOUSE  
EMITTER  
F7425

## lyriQ™ AUDIO MODULE AND INPUTS

PART #	DESCRIPTION
F7396	Single Source, Four-Zone Distribution Module
F7430 <b>COMING SOON!</b>	Four Source, Eight-Zone Distribution Module
F7398	Single Source Input
F7428 <b>COMING SOON!</b>	Triple-Source Input
F7417-WH (White)	Local Source Input
F7417-IV (Ivory)	Local Source Input
F7417-LA (Lt. Almond)	Local Source Input
F7425	Dual IR Mouse Emitter
F7426	Universal IR Target

## lyriQ™ AMPLIFIED VOLUME CONTROLS

PART #	DESCRIPTION
F7394-WH (White)	Amplified Keypad Volume Control With IR
F7394-IV (Ivory)	Amplified Keypad Volume Control With IR
F7394-LA (Lt. Almond)	Amplified Keypad Volume Control with IR
F7399-WH (White)	Amplified Knob Volume Control With IR
F7399-IV (Ivory)	Amplified Knob Volume Control With IR
F7399-LA (Lt. Almond)	Amplified Knob Volume Control With IR