

12VDC, 1.5 Amp Wall Mount Power Supply

PW7760



Powers data networking and video products

features & benefits

specifications

General Info

Type: Power Supply
Housing Material: High Impact Flame Retardant Plastic

Listing Agencies/Third Party Information

cULus: Yes
FCC Standard: Yes
UN SPS C: 39121006

Dimensions

Height Metric: 3.3 cm
Height U S: 1.3"
Length U S: 3.15"
Length Metric: 8 cm
Width Metric: 5 cm
Width U S: 1.97 in

Technical Information

AC Voltage Input: 100-240VAC
Efficiency: 0.7650000000000001
Humidity: Max Noncondensing 85%
m A: 1500 mA
Mounting: Desktop
Operating Temperature Celsius: 0°C to 40°C
Operating Temperature Fahrenheit: 32°F to 104°F
Storage Temperature: -20°C to 60°C
Volts D C: 12 VDC
Watts: 18 W
Receptacle Type: DC Barrel Jack
Number Of Receptacles: 1