

Non-Recessed Nickel F-Connector, White

WP3479-WH



This high quality insert is for use in all Keystone Wall Plates

features & benefits

- Recessed hex nut does not allow for jack rotation
- Contractor packs available in quantities of 50. To order, use part number WP3479-WH-50

specifications

General Info

Color: White
Connection Type: F Connector
Type: Keystone Insert

Listing Agencies/Third Party Information

CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPS C: 39121704

Dimensions

Depth Metric: 3 cm
Depth U S: 1.20"
Length U S: 0.87"
Length Metric: 2.2 cm
Width Metric: 1.7 cm

Width U S: 0.67 in

Technical Information

Material: High Impact Flame Retardant Plastic
Operating Temperature Celsius: -55°C to 155°C
Operating Temperature Fahrenheit: -67°F to 311°F
Output Impedance: 75 ohm
Product Fits Into: Keystone Cutout
Rated Voltage: 500V Peak Voltage Rating