

TracJack Faceplate, two-port (single gang), plastic, Electrical Ivory

OR-40300548-13



Ortronics Single Gang Plastic Faceplates accept front-loading TracJack modules and include two snap-in label fields

features & benefits

- **Low profile design:** Blends with most environments.
- **Recessed label fields:** Supports TIA/EIA 606 standard.
- **Easily accepts snap-in TracJacks:** Easily field configured.
- **Front-load module approach:** Improves access for future work.
- **Textured finish:** Hides future scuffs.
- **Oval mounting holes:** Assists proper alignment

specifications

General Info

Color: Electrical Ivory
Footprint: TracJack
Number Of Ports: 2
Product Series: Clarity
Type: Plates and Boxes

Assembly/Installation Information

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea)

Listing Agencies/Third Party Information

CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

Construction Information

Component1: Plastic TracJack Faceplate

Material1: High Impact Thermoplastic 94V-0 ABS/PC/BLEND

Dimensions

Depth Metric: 7.62 mm

Height Metric: 114.3 mm

Height U S: 4.5"

Width Metric: 69.85 mm

Buy American Act Compliance

Country of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant